



SP-O

Refrigerant split type units
suitable for small-medium cold rooms

- › Condensing unit for floor or roof installation and evaporator for ceiling mounting
- › Reduced installation times and costs
- › Extremely quick mounting thanks to the quick coupling joints
- › Best surface-capacity ratio



Reliable unit with simple and rapid mounting

The SP-O series models are split type units, designed for use in small to medium rooms.

The SP-O series consists of 2 lines: MSP for medium temperatures (max 41m³ at Tc= +0°C, Tamb= +30°C) and BSP for low temperatures (max 30m³ at Tc= -20°C, Tamb= +30°C).

The split structure allows the assembly of evaporator and condenser separately, which ensures that the user has a choice of flexible installation, overcoming all the problems deriving from the lack of space that might prevent the mounting of the monoblock on the room wall.

The condensing unit, protected by a resistant pre-painted sheet steel body and equipped with hermetic compressor, requires a ground installation.

The slim evaporator is positioned on the ceiling of the room allowing to optimize the useful space inside the cold room.

The connection between the two units is realized thanks to pre-charged piping and electrical cables (2,5m, 5m or 10m) which allow quick installation and easy maintenance.

The SP-O systems are supplied ready to use: both the condensing and evaporating units have been tested and precharged with refrigerant, ensuring simple and rapid mounting thanks to specific connecting

joints for the piping.

The SP-O units are equipped with an automatic electric defrosting system.

The option for using the SP-O systems in an external environment including pressure switch or condenser fan speed variator and crankcase heater is available on request.

The control and setting of the unit are simple and intuitive thanks to the electric control panel equipped with electronic control unit.

A wall-mounted remote-control panel completes the equipment, helping to make the SP-O an efficient, reliable and highly customizable machine.

Standard configuration

- › Hermetic compressor
- › Power supply 220-230/1N~/50 or 380-400/3N~/50
- › Air + Axial Fan
- › Remote electronic control panel
- › Expansion through capillary tube
- › Filter on the liquid line
- › Drain heater
- › High and low pressure switches



Personalization options and accessories

Power supply:

- › 220-230/1N~/50 (standard MSP106÷212 and BSP110÷218 units)
- › 380-400/3N~/50 (standard MSP315-320 and BSP220÷330 units)
- › 220-230/1N~/60
- › 220-230/3~/50
- › 220-230/3~/60
- › 440/3~/60
- › 380-400/3N~/60
- › 110-115/1N~/60
- › 460/3~/60

Condensation type:

- › City water with pressure valve

Winter Kit, low ambient temperature accessories:

- › Crankcase heater + Condenser fan pressure switch (only MSP106, MSP107, MSP212, BSP110, BSP112, BSP117, BSP218, BSP220 units)
- › Crankcase heater + Pressure controlled condenser fan speed regulator (only MSP315, MSP320, BSP320, BSP330 units)

Accessories kit:

- › Audible and visual alarm
- › Room light kit
- › Remote control panel for 2-3-4 units
- › Prearrangement for supervision system

Technical data



SP-O

Medium temperature units

Code	SB.MSP106EA11XX	SB.MSP107EA11XX	SB.MSP212EA11XX	SB.MSP315EB11XX	SB.MSP320EB11XX
Refrigerant	R134a	R134a	R134a	R134a	R134a
Power supply [V/Ph~/Hz]	220- 230/1N~/50	220- 230/1N~/50	220- 230/1N~/50	380- 400/3N~/50	380- 400/3N~/50
HP compressor	3/4	1	1,2	3	3,5
Defrost	Electric	Electric	Electric	Electric	Electric
PED category	0	0	0	0	0
Working temperature [°C]	+10 ÷ -5	+10 ÷ -5	+10 ÷ -5	+10 ÷ -5	+10 ÷ -5
Cooling capacity [Watt] [TC=0°C TA=30°C]	1.140	1.422	1.816	3.188	3.492

Low temperature units

Code	SB.BSP110DA11XX	SB.BSP112DA11XX	SB.BSP117DA11XX	SB.BSP218DA11XX	SB.BSP220DB11XX	SB.BSP320DB11XX	SB.BSP330DB11XX
Refrigerant	R452A	R452A	R452A	R452A	R452A	R452A	R452A
Power supply [V/Ph~/Hz]	220- 230/1N~/50	220- 230/1N~/50	220- 230/1N~/50	220- 230/1N~/50	380- 400/3N~/50	380- 400/3N~/50	380- 400/3N~/50
HP compressor	1	1,5	1,7	1,7	2	2	3
Defrost	Electric	Electric	Electric	Electric	Electric	Electric	Electric
PED category	0	0	0	0	0	0	0
Working temperature [°C]	-15 ÷ -25	-15 ÷ -25	-15 ÷ -25	-15 ÷ -25	-15 ÷ -25	-15 ÷ -25	-15 ÷ -25
Cooling capacity [Watt] [TC=-20°C TA=30°C]	662	905	1.164	1.436	1.719	2.384	2.581

Responsible Editor: Zanotti S.p.A. Via M.L. King, 30 · 46020 Pegognaga (MN) · Italy · www.zanotti.com · P.IVA IT01856570203 · REA 220625

The present publication is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this publication to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this publication. All content is copyrighted by Daikin Europe N.V.

ECPEN21-833C

10/2022

