

## Meet our superhero: VRV 5 Heat Recovery



Purpose-built to support the decarbonisation  
of commercial buildings



Lower CO<sub>2</sub>  
equivalents



Industry-leading  
real life efficiencies



Flexibility to take care  
of every room



Variable Refrigerant  
Temperature



BLUEEVOLUTION



We're on a mission to build a sustainable legacy

It is in our DNA to provide safe, healthy and comfortable spaces throughout the building life cycle using world-leading technology. Driven by a dedication to achieve net zero CO<sub>2</sub> emissions by 2050, we work together with our partners and customers in helping to create a world with healthier indoor air and minimal environmental impact.

## Our sustainability values

### Supporting decarbonisation

Our solutions are designed to **support your sustainable goals** by reducing the CO<sub>2</sub> footprint of buildings, whether they are new builds or renovations, thanks to the use of lower GWP refrigerants, high real life seasonal efficiency, smart controls and L∞P by Daikin refrigerant reuse.

### A collective journey

Together with our partners and customers, we are working towards the sustainable transformation of our buildings. We provide expert **support** and **peace of mind** throughout the building life cycle, ensuring **future-proof** solutions for a healthier planet.

### Building for the future

As market leaders in total solutions, we are constantly **innovating to meet your changing needs** and offer you a comfortable, healthy and safe environment.



BLUEEVOLUTION

## Continuing our path to lower CO<sub>2</sub> equivalent solutions

Innovation and adaptation are at the heart of Daikin's decarbonisation strategy. When it comes to refrigerant selection, we have a diversity of choice that we are constantly evaluating to determine the appropriate refrigerant for each application and convert our portfolio to lower GWP refrigerants.

For VRV systems, Daikin has assessed various refrigerants based on four criteria: overall environmental impact, energy efficiency, safety and cost-effectiveness. R-32 was determined to be the most balanced for direct expansion heat pumps.

Since launching the VRV 5 S-series with R-32 in 2020, we continue to expand our VRV portfolio with the launch of the VRV 5 Heat Recovery system and a VRV 5 heat pump in the near future.



VRV 5 S-series  
2020

VRV 5 Heat Recovery  
2022

VRV 5 Heat Pump

### Benefits of R-32

R-32 refrigerant has a lower Global Warming Potential and higher efficiency compared to R-410A, making it the most effective sustainable solution for VRF systems today.

- › **Lower Global Warming Potential (GWP):** only 1/3rd of R-410A
- › **Lower refrigerant charge:** 15% less compared to R-410A
- › **Higher energy efficiency,** greatly reducing the indirect CO<sub>2</sub> eq. impact
- › **Single component refrigerant,** easy to handle and recycle.

### Benefits of VRV systems

VRV systems offer commercial buildings maximum flexibility and peace of mind thanks to the advantages direct expansion (DX) systems have to offer:

- › **More responsive:** Immediate reaction to changing conditions helps avoid overheating
- › **Highly efficient:** Only 2 energy transfer steps are needed (from air to refrigerant, and from refrigerant to air)
- › **Quick and easy to install:** All-in-one box solution without any requirement for field supplied equipment (e.g. gauges, pumps and valves)
- › **Limited space requirements:** All components are integrated, and refrigerant piping is compact.



Lower CO<sub>2</sub> eq. impact,  
better performance and  
maximum flexibility



VRV 5 Heat Recovery ensures maximum comfort and efficiency while significantly reducing a building's environmental footprint. What's more its smart, compact and responsive design makes for flexible and easy installation in any commercial building. In fact, it's not just a single champion device – it's an unstoppable team of heroes assembled in one superpowered system.

#### Sustainability

VRV 5 Heat Recovery is taking sustainable climate control to new heights thanks to its innovative and highly efficient new design.

The VRV system is more sustainable over its entire lifecycle, **reducing the indirect CO<sub>2</sub> eq. impact** thanks to a highly effective 3-pipe heat recovery design and market-leading seasonal efficiency with high η<sub>s,c</sub> values of up to 298.3%. This makes it the perfect partner for your BREEAM, LEED or WELL project.

The system is specifically built for R-32 refrigerant greatly **reducing** the potential **direct CO<sub>2</sub> eq. impact**.

- › 68% less Global Warming Potential (GWP) than R-410A.
- › 15% less refrigerant charge than R-410A.
- › A 71% GWP reduction across the entire system.
- › Single component refrigerant charge, easy to re-use and recycle.

#### Ultra-flexible climate control

Any commercial building can benefit thanks to:

- › Same **pipng flexibility** as R-410A.
- › Unmatched outdoor unit **capacity up to 90kW** in heating.
- › Widest range of dedicated R-32 indoor units on the market.

It can be installed practically anywhere thanks to:

- › Quiet operation via **5 low sound steps**, bringing sound pressure down to 40 dB(A).
- › **High ESP** up to 78Pa allowing concealment indoors.
- › **Wide operation range** up to +46°C in cooling and down to -20°C in heating.

Shîrudo Technology truly sets  
the VRV 5 Heat Recovery apart



With Shîrudo Technology, you have a fully versatile and responsive system that can accurately control the indoor climate of any room or surface.

- › **Peace of mind** as no additional considerations or time-consuming studies are needed.
- › **Factory-integrated** refrigerant response measures, compliant with the IEC product standard, third-party approved by a notified body.
- › **Easy design and selection** thanks to the integration of VRV Xpress floorplan.
- › With built-in Shîrudo Technology, potential leaks are quickly detected and isolated – greatly reducing direct emissions impact.




Want to know more about the IEC product standard and implementation?  
Refer to page 16.



### Quick and easy installation & support

- VRV 5 Heat Recovery offers quick and easy installation thanks to:
- > The **flow through principle**, reducing the number of brazing points and joints needed
  - > A completely redesigned BSSV box that requires **less ceiling height**
  - > A **sliding down PCB** for straightforward servicing.




And never fear, support is always here. You'll have access to an extensive network of experts to make installation and maintenance simple and stress-free.

### A smart approach to comfort

Daikin's signature Variable Refrigerant Temperature ensures maximum comfort and is completely customisable to meet customers' requirements, with the **widest range of specifically designed R-32 indoor units**.

VRV 5 Heat Recovery can match any room size, shape and integration ventilation units for optimum Indoor Air Quality.

And Daikin is committed to constantly innovating its systems to be smarter and easier to control. Our VRV 5 Heat Recovery system is compatible with **Daikin's mini BMS: Intelligent Touch Manager** – a smart energy management system offering real time data for full control of your energy use. For further ease of use, we offer **intuitive online and voice control** via the Onecta app.



VRV 5 outdoor unit overview

		Capacity class (kW)																			
Model	Product name	8	10	12	14	16	18	20	22	24	26	28	VRV indoor units	Residential indoor units	Hydrobox	HRV units VAM	HRV units EKVDX	AHU connection	Air curtains	Remarks	
<p><b>Air-cooled heat recovery</b></p> <p><b>NEW &amp; UNIQUE VRV 5 heat recovery</b></p> <ul style="list-style-type: none"> <li>Reduced CO<sub>2</sub> equivalent thanks to the use of lower GWP refrigerant R-32</li> <li>Top sustainability over the entire lifecycle</li> <li>'Free' heating through heat recovery</li> <li>Tackle small room applications thanks to Shirudo Technology</li> <li>The perfect personal comfort thanks to simultaneous cooling and heating</li> </ul>	 <p>REYA-A</p>	●	●	●	●	●	●	●	●	●	●	○									
		<b>Cooling Capacity</b>	22.4	28.0	33.5	40.0	45.0	50.4	56.0	61.5	67.4	73.5	78.5								
		<b>Heating Capacity</b>	25.0	31.5	37.5	45.0	50.0	56.5	63.0	69.0	75.0	82.5	87.5								

● Single unit, ● Multi combination

Branch selector (BS box) overview

		Capacity class				
Model	Product name	4	6	8	10	12
<p><b>Multi port BS box</b></p> <ul style="list-style-type: none"> <li>Unique range of Branch Selector boxes integrating Shirudo Technology</li> </ul>	 <p>BS-A14AV1B</p>	●	●	●	●	●



VRV 5 outdoor units have the highest capacity on the market – up to 90kW

VRV 5 indoor unit overview

		Capacity class (kW)																
Type	Model	Product name	10	15	20	25	32	40	50	63	71	80	100	125	140	200	250	
Ceiling mounted cassette	<p><b>UNIQUE Round flow cassette</b></p> <p>360° air discharge for optimum efficiency and comfort</p> <ul style="list-style-type: none"> <li>Auto cleaning function ensures high efficiency</li> <li>Intelligent sensors save energy and maximize comfort</li> <li>Flexibility to suit every room layout</li> <li>Lowest installation height in the market!</li> <li>Widest choice ever in decoration panel designs and colors</li> </ul>	 <p>FXFA-A</p>			●	●	●	●	●	●	●	●	●	●				
	<p><b>UNIQUE Fully flat cassette</b></p> <p>Unique design that integrates fully flat into the ceiling</p> <ul style="list-style-type: none"> <li>Perfect integration in standard architectural ceiling tiles</li> <li>Blend of iconic design and engineering excellence</li> <li>Intelligent sensors save energy and maximize comfort</li> <li>Small capacity unit developed for small or well-insulated rooms</li> <li>Flexibility to suit every room layout</li> </ul>	 <p>FXZA-A</p>			●	●	●	●	●	●	●	●	●	●	●			
Concealed ceiling	<p><b>Slim concealed ceiling unit</b></p> <p>Slim design for flexible installation</p> <ul style="list-style-type: none"> <li>Compact dimensions enable installation in narrow ceiling voids</li> <li>Medium external static pressure up to 44Pa</li> <li>Only grilles are visible</li> <li>Small capacity unit developed for small of well-insulated rooms</li> <li>Reduced energy consumption thanks to DC fan motor</li> </ul>	 <p>FXDA-A</p>	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	<p><b>Concealed ceiling unit with medium ESP</b></p> <p>Slimmest yet most powerful medium static pressure unit on the market!</p> <ul style="list-style-type: none"> <li>Slimmest unit in class, only 245mm</li> <li>Low operating sound level</li> <li>Medium external static pressure up to 150Pa facilitates using flexible ducts of varying lengths</li> <li>Automatic air flow adjustment function measures the air volume and static pressure and adjusts it towards the nominal air flow, guaranteeing comfort</li> </ul>	 <p>FXSA-A</p>	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	<p><b>NEW Concealed ceiling unit with high ESP</b></p> <p>ESP up to 270 Pa, ideal for extra large sized spaces</p> <ul style="list-style-type: none"> <li>Optimum comfort guaranteed no matter the length of ductwork or type of grilles, thanks to automatic air flow adjustment</li> <li>Large capacity unit: up to 31.5 kW heating capacity</li> </ul>	 <p>FXMA-A</p>														●	●	●
	<p><b>Wall mounted unit</b></p> <p>For rooms with no false ceilings nor free floor space</p> <ul style="list-style-type: none"> <li>Flat, stylish front panel is more easy to clean</li> <li>Small capacity unit developed for small of well-insulated rooms</li> <li>Reduced energy consumption thanks to DC fan motor</li> <li>The air is comfortably spread up- and downwards thanks to 5 different discharge angles</li> </ul>	 <p>FXAA-A</p>	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
Ceiling suspended	<p><b>NEW Ceiling suspended unit</b></p> <p>For wide rooms with no false ceilings nor free floor space</p> <ul style="list-style-type: none"> <li>Ideal for comfortable air flow in wide rooms thanks to Coanda effect</li> <li>Rooms with ceilings up to 3.8m can be heated or cooled very easily!</li> <li>Can easily be installed in both new and refurbishment projects</li> <li>Can even be mounted in corners or narrow spaces without any problem</li> </ul>	 <p>FXHA-A</p>																●
	<p><b>NEW &amp; UNIQUE 4-way blow ceiling suspended unit</b></p> <p>Unique Daikin unit for high rooms with no false ceilings nor free floor space</p> <ul style="list-style-type: none"> <li>Rooms with ceilings up to 3.5m can be heated up or cooled down very easily!</li> <li>Can easily be installed in both new and refurbishment projects</li> <li>Flexibility to suit every room layout</li> </ul>	 <p>FXUA-A</p>																
<b>Cooling capacity (kW)<sup>(1)</sup></b>			1.1	1.7	2.2	2.8	3.6	4.5	5.6	7.1	8.0	9.0	11.2	14.0	16.0	22.4	28.0	
<b>Heating capacity (kW)<sup>(2)</sup></b>			1.3	1.9	2.5	3.2	4.0	5.0	6.3	8.0	9.0	10.0	12.5	16.0	18.0	25.0	31.5	

(1) Nominal cooling capacities are based on: indoor temperature: 27°CDB, 19°CWB, outdoor temperature: 35°CDB, equivalent refrigerant piping: 5m, level difference: 0m  
 (2) Nominal heating capacities are based on: indoor temperature: 20°CDB, outdoor temperature: 7°CDB, 6°CWB, equivalent refrigerant piping: 5m, level difference: 0m




VRV 5 has the widest range of indoor units specifically designed for R-32 on the market

# Next generation **VRV**




## 7-segment display for quick and accurate error diagnostics

- › Outdoor unit display for quick on-site settings and easy read out of errors
- › Indication of service parameters for checking basic functions



## Refrigerant-cooled PCB

- › Reliable cooling because it is not influenced by ambient air temperature
- › Smaller switchbox for smoother air flow through the heat exchanger, increasing heat exchange efficiency by 5%




## Unmatched piping flexibility

- › Longest length up to 165m
- › Total length 1,000m



## Asymmetric fan design

- › High ESP up to 78Pa to allow ducting
- › Low sound levels down to 40 dB(A)



## 4-sided, 3-row heat exchanger

- › Thanks to the large surface of the heat exchanger (up to 235m<sup>2</sup>) VRV units are compact, light and highly efficient



## New inverter compressor

- › Specifically developed for R-32 refrigerant
- › Back pressure control increasing efficiency in low load operation

# Advantages of 3-pipe technology


## “Free” heat production

An integrated heat recovery system reuses heat from offices and server rooms to warm other areas.

## Maximum comfort

A VRV heat recovery system allows simultaneous cooling and heating.


- › For hotel owners, this means they can freely choose between cooling or heating to create a perfect environment for guests.
- › For offices, it means a perfect working indoor climate for both north and south-facing offices.



## More “free” heat


Daikin 3-pipe technology needs less energy to recover heat, meaning significantly higher efficiency during heat recovery mode. Our system can recover heat at a low condensing temperature because it has dedicated gas, liquid and discharge pipes.

In a 2-pipe system, gas and liquid travel as a mixture so the condensing temperature needs to be higher in order to separate the mixed gas and liquid refrigerant. The higher condensing temperature means more energy is used to recover heat resulting in lower efficiency.



## Lower pressure drop means more efficiency


- › Smooth refrigerant flow in 3-pipe system thanks to 2 smaller gas pipes results in higher energy efficiency
- › Disturbed refrigerant flow in large gas pipe on 2-pipe system results in larger pressure drop



# VRV 5 Heat Recovery

Purpose-built to support the decarbonisation of commercial buildings

- › Reduced CO<sub>2</sub> equivalent thanks to the use of lower GWP R-32 refrigerant and lower refrigerant charge
- › Single component refrigerant, easy to re-use and recycle
- › Greatest sustainability over the entire lifecycle, thanks to market leading real-life seasonal efficiency
- › “Free” heating through efficient 3-pipe heat recovery, transferring heat from areas requiring cooling to areas requiring heating
- › Tackle small room applications without any additional measures, thanks to Shirudo Technology
- › Specially designed indoor units for R-32, ensuring low sound and maximum efficiency
- › Simultaneous cooling and heating for the perfect personal comfort of guests/tenants
- › Like for like R-410A installation flexibility with piping lengths up to 165 meters and a total length of 1,000 meters
- › Sound pressure down to 40 dB(A) thanks to 5 low sound steps
- › ESP up to 78 Pa to allow ducting
- › Wide operation range of up to +46°C in cooling and down to -20°C in heating



Lower CO<sub>2</sub> equivalents



5 low sound steps



More details and final information can be found by scanning or clicking the QR codes.

Outdoor unit	REYA	8A	10A	12A	14A	16A	18A	20A
Capacity range	HP	8	10	12	14	16	18	20
Cooling capacity	Prated,c	kW	22.4	28.0	33.5	40.0	45.0	50.4
Heating capacity	Prated,h	kW	22.4	28.0	33.5	40.0	45.0	50.4
	Max.	6°CWB	kW	25.0	31.5	37.5	45.0	50.0
Recommended combination		4 x FXFA50A2VEB	4 x FXFA63A2VEB	6 x FXFA50A2VEB	1 x FXFA50A2VEB + 5 x FXFA63A2VEB	4 x FXFA63A2VEB + 2 x FXFA80A2VEB	3 x FXFA50A2VEB + 5 x FXFA63A2VEB	2 x FXFA50A2VEB + 6 x FXFA63A2VEB
η <sub>s,c</sub>	%	290.8	282.6	285.3	306.1	281.0	280.6	262.2
η <sub>s,h</sub>	%	161.5	170.2	176.4	168.3	167.5	172.5	162.7
SEER		7.35	7.14	7.21	7.73	7.10	7.09	6.63
SCOP		4.11	4.33	4.49	4.28	4.26	4.39	4.14
Maximum number of connectable indoor units		64						
Indoor index connection	Min.	100	125	150	175	200	225	250
	Max.	260	325	390	455	520	585	650
Dimensions	Unit	HeightxWidthxDepth			mm			
		1,685 x 930 x 765			1,685 x 1,240 x 765			
Weight	Unit	kg			kg			
		213			296		319	
Sound power level	Cooling	Nom.	78.3	78.8	82.5	78.7	83.4	87.9
Sound pressure level	Cooling	Nom.	56.3	58.0	60.8	58.1	61.4	67.0
Operation range	Cooling	Min.~Max.	°CDB					
	Heating	Min.~Max.	°CWB					
			-5 ~46					
			-20 ~16					
Refrigerant	Type/GWP	R-32/675.0						
	Charge	kg/TCO <sub>2</sub> Eq			kg/TCO <sub>2</sub> Eq			
		9.00 / 6.08			10.6 / 7.16			
Piping connections	Liquid	OD	9.52	12.70				
	Gas	OD	19.1	22.2		28.6		
	HP/LP gas	OD	15.90	19.10		22.20		
	Total piping length	System	Actual		m			
			1,000					
Power supply	Phase/Frequency/Voltage	Hz/V						
		3N~/50 /380-415						
Current - 50Hz	Maximum fuse amps (MFA)	A	20	25	32	40	50	



Completely redesigned BSSV boxes for faster installation and easier servicing



Widest R-32 VRV range in the market

Outdoor unit System	REYA	10A	13A	16A	18A	20A	22A	24A	26A	28A	
System	Outdoor unit module 1	REMA5A		REYA8A		REYA10A		REYA12A		REYA16A	
	Outdoor unit module 2	REMA5A	REYA8A	REYA10A	REYA12A	REYA16A	REYA14A	REYA16A			
Capacity range	HP	10	13	16	18	20	22	24	26	28	
Cooling capacity	Prated,c	kW	28.0	36.4	44.8	50.4	55.9	61.5	67.4	73.5	
Heating capacity	Prated,h	kW	28.0	36.4	44.8	50.4	55.9	61.5	67.4	73.5	
	Max.	6°CWB	kW	32.0	41.0	50.0	56.5	62.5	69.0	75.0	
Recommended combination		4 x FXFA63A2VEB	3 x FXFA50A2VEB + 3 x FXFA63A2VEB	4 x FXFA63A2VEB + 2 x FXFA80A2VEB	4 x FXFA50A2VEB + 4 x FXFA63A2VEB	10 x FXFA50A2VEB	6 x FXFA50A2VEB + 4 x FXFA63A2VEB	4 x FXFA50A2VEB + 4 x FXFA63A2VEB + 2 x FXFA80A2VEB	7 x FXFA50A2VEB + 5 x FXFA63A2VEB	6 x FXFA50A2VEB + 4 x FXFA63A2VEB + 2 x FXFA80A2VEB	
η <sub>s,c</sub>	%	301.9	296.5	293.0	287.5	287.6	283.6	283.4	296.2	282.8	
η <sub>s,h</sub>	%	160.6	161.5	170.9	170.5	172.2	173.3	165.2	172.0	171.5	
SEER		7.62	7.49	7.40	7.26	7.27	7.17	7.16	7.48	7.15	
SCOP		4.09	4.11	4.35	4.34	4.38	4.41	4.20	4.38	4.36	
Maximum number of connectable indoor units		64									
Indoor index connection	Min.	125	163	200	225	250	275	300	325	350	
	Max.	325	423	520	585	650	715	780	845	910	
Piping connections	Liquid	OD	9.52	12.70				15.90			
	Gas	OD	19.1	22.2		28.6					
	HP/LP gas	OD	15.90	19.10		22.20					
	Total piping length	System	Actual		m				1,000		
			500								
Power supply	Phase/Frequency/Voltage	Hz/V									
		3N~/50 /380-415									
Current - 50Hz	Maximum fuse amps (MFA)	A	40	50	63						

Outdoor unit module	REMA	5A
Dimensions	Unit	HeightxWidthxDepth
		1,685 x 930 x 765
Weight	Unit	kg
		213
Fan	External static pressure	Pa
	Max.	78
Sound power level	Cooling	Nom.
		78.3
Sound pressure level	Cooling	Nom.
		56.3
Operation range	Cooling	Min.~Max.
	Heating	Min.~Max.
		°CDB
		°CWB
		-5 ~46
		-20 ~16
Refrigerant	Type/GWP	R-32/675.0
	Charge	kg/TCO <sub>2</sub> Eq
		9.00 / 6.08
Power supply	Phase/Frequency/Voltage	Hz/V
		3N~/50 /380-415
Current - 50Hz	Maximum fuse amps (MFA)	A
		20

Actual number of connectable indoor units depends on the indoor unit type and the connection ratio restriction for the system (50% ≤ CR ≤ 120%) | Contains fluorinated greenhouse gases | \* EU member states, UK, Bosnia-Herzegovina, Serbia, Montenegro, Kosovo, Albania, North Macedonia, Iceland, Norway, Switzerland

# Multi branch selector (BSSV) for VRV 5 Heat Recovery

## Specifically developed for lower GWP R-32

- › **Reduced CO<sub>2</sub> equivalent** thanks to the use of lower GWP R-32 refrigerant and lower refrigerant charge
- › Unique range of multi BS boxes allowing **efficient 3-pipe** heat recovery
- › No limitation on room size, thanks to **Shirudo Technology** (1)  
The integrated shut-off valves in the BSSV box ensure that in case of a refrigerant leak only the specific branch is closed off.



- › Unique range of multi BS boxes allowing efficient 3-pipe heat recovery
- › **NEW** No limitation on room size, thanks to Shirudo Technology (1)
- › **NEW** Faster installation thanks to Refrigerant Flow Through reducing the number of brazing points and joint kits
- › **NEW** Easy servicing in false ceilings thanks to sliding down PCB
- › **NEW** Limited ceiling void required as the box can be installed at just 5mm from the ceiling
- › **NEW** Quick on-site settings, indication of service parameters and easy read out of errors thanks to 7 segment display
- › Up to 16kW capacity available per port
- › Connect up to 250 class unit (28kW) by combining 2 ports
- › No limit on unused ports allowing phased installation
- › Faster installation thanks to open port connection
- › Allows multi tenant applications
- › Connectable to REYA-A heat recovery units




BS6A14AV1B


## Completely redesigned for faster installation and easier servicing

- › Faster installation thanks to **Refrigerant Flow Through** reducing the number of brazing points and joint kits


VRV 5: only 24 brazings point and no joint kits



VRV 5: 39 brazing points and 3 joint kits



- › Easy servicing in false ceilings thanks to **sliding down PCB**



- › Limited ceiling void required as the box can be installed at just 5mm from the ceiling

More details and final information can be found by scanning or clicking the QR codes.



BS-A14AV1B

Branch selector	BS	4A14AV1B	6A14AV1B	8A14AV1B	10A14AV1B	12A14AV1B
Maximum number of connectable indoor units		20	30	40	50	60
Maximum number of connectable indoor units per branch				5		
Number of branches		4	6	8	10	12
Maximum capacity index of connectable indoor units		400	600		750	
Maximum capacity index of connectable indoor units per branch				140 (250 if 2 ports are combined)		
Dimensions	Unit	HeightxWidthxDepth		mm		
		291x600x845		291x1,000x845		291x1,400x845
Weight	Unit	kg				
		40		56	65	83
Casing	Material	Galvanised steel plate				
Piping connections	Outdoor unit or Refrigerant Flow Through	Liquid	Type	Brazing connection		
			OD	9.5 (2) / 12.7 (2) / 15.9		
	Gas	Type	Brazing connection			
		OD	15.9 (2) / 19.1(2) / 22.2(2) / 28.6			
	Discharge gas	Type	Brazing connection			
		OD	12.7 (2) / 15.9(2) / 19.1(2) / 22.2			
	Indoor unit	Liquid	Type	Brazing connection		
			OD	6.4(3) / 9.5 (4)		
	Gas	Type	Brazing connection			
		OD	9.5 (5) / 12.7 (6) / 15.9 (4)			
Drain		VP20 (I.D. 20/O.D. 26)				
BS units connected in Refrigerant Flow Through	Maximum allowed amount of BS units	4				
	Maximum total number of ports of BS units	16				
	Maximum total capacity index of indoor unit	750				
Sound absorbing thermal insulation		Urethane foam, polyethylene foam				
BS box system safety requirements	Dust connection diameter on unit	mm				
	Dust connection positions	Left/Right				
Power supply	Phase	1~				
	Frequency	Hz				
	Voltage	V				
	Maximum fuse amps (MFA)	A				


Contains fluorinated greenhouse gases | (1) Refer to Xpress selection software to ensure compliance to specific product standard. Field supplied duct and fan might be required to install the BS box in very small spaces | (2) Accessory pipe required | (3) When connecting indoor units smaller or equal to 80 class (no need to cut the outlet pipe) | (4) When connecting indoor units larger or equal to 100 class (the outlet pipe needs to be cut) | (5) When connecting indoor units smaller or equal to 32 class (no need to cut the outlet pipe) | (6) When connecting indoor units between 40 & 80 class (the outlet pipe needs to be cut)

# Did you know ...

different standards regarding F-gas safety regulations exist?

- Refrigerants can be classified according to 2 safety groups:
- › Flammability (1, 2L, 2, 3): covered by the specific heat pump standard **IEC60335-2-40 (Ed. 6)** as it prevails over EN378:2016
  - › Toxicity (A or B): covered by the generic standard on refrigerants **EN378:2016**.

Shirudo Technology focuses on offering maximum flexibility within the IEC60335-2-40 (Ed.6) requirements as limitations for flammability of A2L refrigerants are stricter than the ones for toxicity.



# Peace of mind



With Shirudo Technology, Daikin ensures compliance to the product standard IEC60335-2-40 (Ed. 6) for indoor units. With factory-integrated refrigerant control measures, these systems are also the quickest and most flexible to design.

There is **no need for complex and time consuming calculations**, even for small room applications. And BSSV boxes come with a ventilated enclosure for quick and simple integration of any potential additional measures – making installation in demanding spaces easier than ever.

For stress free design of any commercial building, validate your project in our Xpress software, featuring floor plan integration.

## Refrigerant control measures factory-integrated

Shirudo Technology includes 2 factory measures and sensors built into a VRV 5 system.

**Integrated sensors to detect refrigerant leak.**  
Leak detection activates:

- 1 Audible and visual alarm**
  - › Integrated in the Madoka wired remote controller
  - › In case an additional supervisor alarm is needed it can be easily integrated
- 2 Refrigerant recovery and shut-off valves**
  - › Shut off valves of the affected refrigerant branch are closed, containing the leak
  - › The rest of the system remains in operation

Example for VRV 5 Heat Recovery

## Compliance taken care of

- › No study or calculations needed on where and how to install outdoor or indoor units.
- › No need for studies to decide if and what safety measures are required.
- › Third party CB certified by a notified body (SGS CEBC).

## Automatic, real time leak detection and refrigerant containment controls

- › Fully compliant to product standard (IEC60335-2-40), reducing the risk of direct CO<sub>2</sub> eq. impact from a refrigerant leak.
- › Real time leak detection sensors, triggering refrigerant containment safety measures in the unlikely event of a leak.

(1) Refer to Xpress selection software to ensure compliance to specific product standard. Field supplied duct and fan may be required to install the BS box in very small spaces.


# VRV 5 S-series

## VRV 5 indoor unit benefit overview

		Ceiling mounted cassette units		Concealed ceiling units			Wall mounted unit	Ceiling suspended units	
		FXFA-A	FXZA-A	FXDA-A	FXSA-A	NEW FXMA	FXAA-A	NEW FXHA-A	NEW FXUA-A
We care	Home leave operation	●	●	●	●	●	●	●	●
	Fan only	●	●	●	●	●	●	●	●
	Auto cleaning filter	○		○					
	Floor and presence sensor	○	○						○ NEW
Comfort	Draught prevention	●	●						●
	Whisper quiet	●	●	●	●		●		
	Auto cooling-heating changeover	●	●	●	●	●	●	●	●
Air treatment	Air filter	● (2)	● (2)	● (2)	● (2)	● (2)	● (2)	● (2)	● (2)
Humidity control	Dry programme	●	●	●	●	●	●	●	●
	Ceiling soiling prevention	●	●						
Air flow	Vertical auto swing	●	●				●	●	●
	Fan speed steps	5 + auto	3 + auto	3	3 + auto	3 (50-125) 3 + auto (200-250)	3 + auto	3	3 + auto
	Individual flap control	●	●						●
Remote control & timer	Onecta controller (BRP069C51)	○	○	○	○	○	○	○	○
	Weekly timer	○	○	○	○	○	○	○	○
	Infrared remote control	○ (1)	○ (1)	○ (1)	○ (1)	○ (1)	○ (1)	○ (1)	○ (1)
	Wired remote control	● (3)	● (3)	● (3)	● (3)	● (3)	● (3)	● (3)	● (3)
	Centralised control	○	○	○	○	○	○	○	○
Other functions	Auto-restart	●	●	●	●	●	●	●	●
	Self-diagnosis	●	●	●	●	●	●	●	●
	Drain pump kit	●	●	●	●	●	○	○	●
	Multi tenant	● (4)	● (4)	○ (4)	○ (4)	○ (4)	○ (4)	○ (4)	○ (4)

● standard, ○ optional

(1) Must be combined with Madoka wired remote controller.  
 (2) Pre filter  
 (3) BRCH52W/S/K is a required option  
 (4) Only in combination with REYA outdoor units





The most comfortable cassette  
just got better

## New round flow cassette




- › **Bigger louvers** and **new sensor logic** further improves equal air distribution in the room
- › **Widest ever choice in panels** for cassette units, with up to 8 different panels



- › Comes with the known benefits: **360° air flow discharge** and **intelligent sensors**

- › **Auto cleaning** panels available in black and white



### Auto cleaning filter

Dust can simply be removed using a vacuum cleaner without opening the unit.

\* Available as an option

FXFA-A




BLUEVOLUTION


## Round flow cassette

360° air discharge for optimum efficiency and comfort

- › Optimised design for R-32 refrigerant
- › Optional automatic filter cleaning panel results in higher efficiency & comfort and lower maintenance costs.
- › Two optional intelligent sensors improve energy efficiency and comfort
- › Widest choice ever in decoration panels: designer panels in white (RAL9010) and black (RAL9005) and standard panels in white (RAL9010) with grey louvers or full white
- › Bigger flaps and unique swing pattern improve equal air distribution
- › Individual flap control: flexibility to suit every room layout without changing the location of the unit!
- › Lowest installation height in the market: 214mm for class 20-63
- › Optional fresh air intake
- › Standard drain pump with 675mm lift increases flexibility and installation speed



FXFA-A



BRC1H52W, BRP069C51



White panel

White auto cleaning panel

Black panel

Black design panel



More details and final information can be found by scanning or clicking the QR codes.




Indoor Unit		FXFA	20A	25A	32A	40A	50A	63A	80A	100A	125A		
Cooling capacity	Total capacity	kW	2.20	2.80	3.60	4.50	5.60	7.10	9.00	11.20	14.00		
	At high fan speed	kW	2.50	3.20	4.00	5.00	6.30	8.00	10.00	12.50	16.00		
Heating capacity	Total capacity	kW		0.017		0.018	0.023	0.028	0.045	0.078	0.103		
	At high fan speed	kW		0.017		0.018	0.023	0.028	0.045	0.078	0.103		
Power input – 50Hz	Cooling	kW											
	Heating	kW											
Dimensions	Unit	mm	204x840x840			246x840x840			288x840x840				
	HeightxWidthxDepth	mm	18			19			21				
Weight	Unit	kg	18			19			21				
Casing	Material		Galvanised steel plate										
Decoration panel	Model		Standard panels: BYCQ140E – white with grey louvers / BYCQ140EW – full white / BYCQ140EB – black Auto cleaning panels: BYCQ140EGF – white / BYCQ140EGFB – black Designer panels: BYCQ140EP – white / BYCQ140EPB – black										
	Dimensions	HeightxWidthxDepth	mm	Standard panels: 65x950x950 / Auto cleaning panels: 148x950x950 / Designer panels: 106x950x950									
Fan	Air flow rate – 50Hz	Cooling	H/MH/M/ML/L	m <sup>3</sup> /min	12.8/11.8/10.7/9.8/8.9		14.8/13.7/12.6/11.5/10.4	15.1/14.0/12.8/11.8/10.7	16.6/15.0/13.3/12.0/10.7	23.3/21.7/19.3/17.5/13.8	28.8/25.1/21.2/17.5/13.8	33.0/30.2/27.4/24.0/20.6	
			Heating	H/MH/M/ML/L	m <sup>3</sup> /min	12.8/11.8/10.7/9.8/8.9		14.8/13.7/12.6/11.5/10.4	15.1/14.0/12.8/11.8/10.7	16.6/15.0/13.3/12.0/10.7	23.3/21.7/19.3/16.5/13.8	29.0/25.1/21.2/17.5/13.8	33.0/30.2/27.4/24.0/20.6
Air filter	Type		Resin net										
Sound power level	Cooling	At high fan speed	dB(A)	49.0 (4)			51.0 (4)			53.0 (4)	55.0 (4)	60.0 (4)	61.0 (4)
	Heating	H/MH/M/ML/L	dB(A)	31.0/30.0/29.0/29.5/28.0 (4)			33.0/32.0/31.0/30.0/29.0 (4)			35.0/34.0/33.0/32.0/30.0 (4)	38.0/36.0/34.0/32.0/30.0 (4)	43.0/41.0/37.0/34.0/30.0 (4)	45.0/43.0/41.0/39.0/36.0 (4)
Sound pressure level	Cooling	H/MH/M/ML/L	dB(A)	31.0/30.0/29.0/29.5/28.0 (4)			33.0/32.0/31.0/30.0/29.0 (4)			35.0/34.0/33.0/32.0/30.0 (4)	38.0/36.0/34.0/32.0/30.0 (4)	43.0/41.0/37.0/34.0/30.0 (4)	45.0/43.0/41.0/39.0/36.0 (4)
	Heating	H/MH/M/ML/L	dB(A)	31.0/30.0/29.0/29.5/28.0 (4)			33.0/32.0/31.0/30.0/29.0 (4)			35.0/34.0/33.0/32.0/30.0 (4)	38.0/36.0/34.0/32.0/30.0 (4)	43.0/41.0/37.0/34.0/30.0 (4)	45.0/43.0/41.0/39.0/36.0 (4)
Refrigerant	Type/GWP		R-32/675.0										
Piping connections	Liquid	OD	mm	6.35			6.35			9.52			
	Gas	OD	mm	9.52			12.70			15.90			
Drain			VP25 (O.D. 32 / I.D. 25)										
Power supply	Phase/Frequency/Voltage	Hz/V	1~/50/60/220-240/220										
Current – 50Hz	Maximum fuse amps (MFA)	A	6										
Control systems	Infrared remote control		BRC7FA532F / BRC7FB532F / BRC7FA532FB / BRC7FB532FB (2)										
	Wired remote control		BRC1H52W/S/K										

(1) MFA is used to select the circuit breaker and the ground fault circuit interrupter (earth leakage circuit breaker). For more detailed information on each combination, please refer to the electrical data drawing | (2) Must be combined with Madoka wired remote controller. | (3) L/ML/M/MH/H are the different fan speeds available. L= low; ML= medium low; M= medium; MH= medium high; H= high | (4) Sound of designer panel: +3dB | Contains fluorinated greenhouse gases

# Fully Flat Cassette

## Design & Genius in one



### Why choose fully flat cassette

- › Unique design in the market that integrates fully flat into the ceiling
- › Advanced technology and top efficiency combined
- › Most quiet cassette available on the market

### FXZQ-A



Choice between grey or white panel

### Benefits for the installer

- › Unique product in the market!
- › Most quiet unit (25dBA)
- › The user-friendly remote control, available in several languages, enables the easy set-up of sensor option and control of the individual flap position
- › Meeting European design taste.

### Benefits for the consultant

- › Unique product in the market!
- › Blends seamlessly in any modern office interior design
- › Ideal product to improve BREEAM score/EPBD in combination with Sky Air (FFA\*) or VRV IV heat pump units (FXZQ\*).

### Benefits for the end user

- › Engineering excellence and unique design in one
- › Most quiet unit (25dBA)
- › Perfect working conditions: no more cold draughts
- › Save up to 27% on your energy bill thanks to the optional sensors
- › Flexible usage of space and suits any room configuration thanks to individual flap control
- › User-friendly remote control, available in several languages.


### FXZA-A

BLUEEVOLUTION


## Fully flat cassette

Unique design in the market that integrates fully flat into the ceiling


- › Optimised design for R-32 refrigerant
- › Fully flat integration in standard architectural ceiling tiles, leaving only 8mm
- › Remarkable blend of iconic design and engineering excellence with an elegant finish in white or a combination of silver and white
- › Two optional intelligent sensors improve energy efficiency and comfort
- › 15 class unit especially developed for small or well-insulated rooms, such as hotel bedrooms, small offices, etc.
- › Individual flap control: flexibility to suit every room layout without changing the location of the unit!



- › Optional fresh air intake
- › Standard drain pump with 630mm lift increases flexibility and installation speed



FXZA-A



BRC1H52W, BRP069C51

amazon alexa

works with the Google Assistant




More details and final information can be found by scanning or clicking the QR codes.



Indoor Unit		FXZA		15A	20A	25A	32A	40A	50A		
Cooling capacity	Total capacity	At high fan speed		kW	1.70	2.20	2.80	3.60	4.50	5.60	
	Heating capacity	Total capacity	At high fan speed		kW	1.90	2.50	3.20	4.00	5.00	6.30
Power input – 50Hz	Cooling	At high fan speed		kW	0.018		0.020	0.019	0.029	0.048	
	Heating	At high fan speed		kW	0.018		0.020	0.019	0.029	0.048	
Dimensions	Unit	HeightxWidthxDepth		mm	260 x575 x575						
Weight	Unit			kg	15.5		16.5		18.5		
Casing	Material	Galvanised steel plate									
Decoration panel	Model	BYFQ60C4W1W									
	Colour	White (N9.5)									
	Dimensions	HeightxWidthxDepth		mm	46 x620 x620						
Decoration panel 2	Model	BYFQ60C4W1S									
	Colour	SILVER									
	Dimensions	HeightxWidthxDepth		mm	46 x620 x620						
Decoration panel 3	Model	BYFQ60B3W1 + wire harness EKRS23									
	Colour	WHITE (RAL9010)									
	Dimensions	HeightxWidthxDepth		mm	55 x700 x700						
Fan	Air flow rate – 50Hz	Cooling	At high/medium/low fan speed		m <sup>3</sup> /min	8.5/7.0/6.5	8.7/7.5/6.5	9.0/8.0/6.5	10.0/8.5/7.0	11.5/9.5/8.0	14.0/12.5/10.0
		Heating	At high/medium/low fan speed		m <sup>3</sup> /min	8.5/7.0/6.5	8.7/7.5/6.5	9.0/8.0/6.5	10.0/8.5/7.0	11.5/9.5/8.0	14.0/12.5/10.0
Air filter	Type	Resin net									
Sound power level	Cooling	At high fan speed		dBA	49		50	51	54	60	
	Heating	At high/medium/low fan speed		dBA	31.5/28.0/25.5	32.0/29.5/25.5	33.0/30.0/25.5	33.5/30.0/26.0	37.0/32.0/28.0	43.0/40.0/33.0	
Sound pressure level	Cooling	At high/medium/low fan speed		dBA	31.5/28.0/25.5	32.0/29.5/25.5	33.0/30.0/25.5	33.5/30.0/26.0	37.0/32.0/28.0	43.0/40.0/33.0	
	Heating	At high/medium/low fan speed		dBA	31.5/28.0/25.5	32.0/29.5/25.5	33.0/30.0/25.5	33.5/30.0/26.0	37.0/32.0/28.0	43.0/40.0/33.0	
Refrigerant	Type/GWP	R-32/675.0									
Piping connections	Liquid	OD			mm	6.35					
		Gas			mm	9.52		12.70			
	Drain				VP20 (I.D. 20/O.D. 26)						
Power supply	Phase/Frequency/Voltage			Hz/V	1~/50/60/220-240/220						
Current – 50Hz	Maximum fuse amps (MFA)			A	6						
Control systems	Infrared remote control	BRC7F530W (white panel) / BRC7F530S (grey panel) / BRC7EB530W (standard panel) (1)									
Control systems	Wired remote control	BRC1H52W/S/K									

Dimensions do not include control box | (1) Must be combined with Madoka wired remote controller\* feature | Contains fluorinated greenhouse gases


## Auto cleaning filter for concealed ceiling units



## The unique automatic cleaning filter achieves higher efficiency and comfort with lower maintenance costs

### Reduce running costs

- › Automatic filter cleaning ensures low maintenance costs because the filter is always clean



### Minimal time required for filter cleaning

- › The dust box can be emptied with a vacuum cleaner for fast and easy cleaning
- › No more dirty ceilings

### Improved indoor air quality

- › Optimum airflow eliminates draft and insulates sound

### Superb reliability

- › Prevents clogged filters for seamless operation


### Unique technology

- › Unique and innovative filter technology inspired by the Daikin auto cleaning cassette



### Combination table

	Split / Sky Air				VRV						
	FDXM-F9				FXDA-A/FXDQ-A3						
	25	35	50	60	15	20	25	32	40	50	63
BAE20A62	•	•			•	•	•	•			
BAE20A82									•	•	
BAE20A102			•	•							•



## How does it work?

- 1 Scheduled automatic filter cleaning
- 2 Dust collects in a dust box that's integrated into the unit
- 3 The dust can easily be removed with a vacuum cleaner



### Specifications

	BAE20A62	BAE20A82	BAE20A102
Height (mm)		210	
Width (mm)	830	1,030	1,230
Depth (mm)		188	

## FXDA-A

## Slim concealed ceiling unit


### Slim design for flexible installation

- › Optimised design for R-32 refrigerant
- › 10 class unit especially developed for small or well-insulated rooms, such as hotel bedrooms, small offices, etc.
- › Compact dimensions, can easily be mounted in a ceiling void of only 240mm


SERIE A (15, 20, 25, 32)



- › Medium external static pressure up to 44Pa facilitates unit use with flexible ducts of varying lengths
- › Discretely concealed in the wall: only the suction and discharge grilles are visible
- › Optional auto cleaning filter option ensures maximum efficiency, comfort and reliability by regular filter cleaning
- › Flexible installation, as the air suction direction can be altered from rear to bottom suction



- › Standard drain pump with 600mm lift increases flexibility and installation speed





More details and final information can be found by scanning or clicking the QR codes.



FXDA-A

Indoor Unit				FXDA	10A	15A	20A	25A	32A	40A	50A	63A		
Cooling capacity	Total capacity	At high fan speed		kW	1.10	1.70	2.20	2.80	3.60	4.50	5.60	7.10		
Heating capacity	Total capacity	At high fan speed		kW	1.30	1.90	2.50	3.20	4.00	5.00	6.30	8.00		
Power input - 50Hz	Cooling	At high fan speed		kW	0.026	0.035	0.030	0.035	0.038	0.049	0.058			
		Heating	At high fan speed	kW	0.026	0.035	0.030	0.035	0.038	0.049	0.058			
Required ceiling void >				mm	240									
Dimensions	Unit	HeightxWidthxDepth		mm	200x750x620			200x950x620			200x1,150x620			
Weight	Unit			kg	22.0		23.0		26.5		30.5			
Casing	Material		Galvanised steel											
Fan	Air flow rate - 50Hz	Cooling	At high/medium/low fan speed	m <sup>3</sup> /min	5.2/4.9/4.7	6.5/6.2/5.8	8.0/7.2/6.4		10.5/9.5/8.5		12.5/11.0/10.0		16.5/14.5/13.0	
		Heating	At high/medium/low fan speed	m <sup>3</sup> /min	5.2/4.9/4.7	6.5/6.2/5.8	8.0/7.2/6.4		10.5/9.5/8.5		12.5/11.0/10.0		16.5/14.5/13.0	
	External static pressure - 50Hz	Factory set / High		Pa	10/30			15/44						
Air filter	Type		Removable / washable											
Sound power level	Cooling	At high fan speed		dB(A)	48	50	51		52	53	54			
Sound pressure level	Cooling	At high/medium/low fan speed		dB(A)	29.0/28.0/26.0	32.0/31.0/27.0	33.0/31.0/27.0		34.0/32.0/28.0	35.0/33.0/29.0	36.0/34.0/30.0			
		At high/medium/low fan speed		dB(A)	29.0/28.0/26.0	32.0/31.0/27.0	33.0/31.0/27.0		34.0/32.0/28.0	35.0/33.0/29.0	36.0/34.0/30.0			
Refrigerant	Type/GWP		R-32/675.0											
Piping connections	Liquid	OD		mm	6.35									
		Gas	OD	mm	9.52		12.70							
	Drain	VP20 (I.D. 20/O.D. 26)												
Power supply	Phase/Frequency/Voltage		Hz/V		1~/50/60/220-240/220									
Current - 50Hz	Maximum fuse amps (MFA)		A		6									
Control systems	Infrared remote control		BRC4C65 / BRC4C66 (1)											
	Wired remote control		BRC1H52W/S/K											

(1) Must be combined with Madoka wired remote controller | Contains fluorinated greenhouse gases



Auto cleaning filter option


# Concealed ceiling unit with medium ESP

Slimmest yet most powerful medium static pressure unit on the market


- Optimised design for R-32 refrigerant
- Slimmest unit in class, only 245mm (300mm built-in height) and therefore narrow ceiling voids are no longer a challenge




- Quiet operation: down to 25dBA sound pressure level
- Medium external static pressure up to 150Pa facilitates using flexible ducts of varying lengths
- Possibility to change ESP via wired remote control allows optimisation of the supply air volume
- Discretely concealed in the wall: only the suction and discharge grilles are visible
- 15 class unit especially developed for small or well-insulated rooms, such as hotel bedrooms, small offices, etc.
- Optional fresh air intake
- Fresh air intake integrated in the same system thus reducing installation cost as no additional ventilation device is required



\* Brings in up to 10% of fresh air into the room



- Standard built-in drain pump with 625mm lift increases flexibility and installation speed




### Automatic Airflow Adjustment function

Automatically selects the most appropriate fan curve to achieve the units' nominal air flow within ±10%

#### Why?

After installation the real ducting will frequently differ from the initially calculated air flow resistance \* the real air flow may be much lower or higher than nominal, leading to a lack of capacity or uncomfortable air temperature. Automatic Airflow Adjustment function will adapt the unit's fan speed to any ducting automatically (10 or more fan curves are available on every model), making installation much faster



More details and final information can be found by scanning or clicking the QR codes.


Indoor Unit		FXSA	15A	20A	25A	32A	40A	50A	63A	80A	100A	125A	140A	
Cooling capacity	Total capacity	kW	1.70	2.20	2.80	3.60	4.50	5.60	7.10	9.00	11.20	14.00	16.00	
	At high fan speed	kW												
Heating capacity	Total capacity	kW	1.90	2.50	3.20	4.00	5.00	6.30	8.00	10.00	12.50	16.00	18.00	
	At high fan speed	kW												
Power input - 50Hz	Cooling	kW	0.046		0.049	0.094	0.096	0.106	0.143	0.176	0.216	0.272		
	Heating	kW	0.046		0.049	0.094	0.096	0.106	0.143	0.176	0.216	0.272		
Dimensions	Unit	mm	245x550x800				245x700x800			245x1,000x800		245x1,400x800		245x1,550x800
	HeightxWidthxDepth	mm	245x550x800				245x700x800			245x1,000x800		245x1,400x800		245x1,550x800
Weight	Unit	kg	23.5		24.0	28.5	29.0	35.5	36.5	46.0	47.0	51.0		
Casing	Material		Galvanised steel plate											
Fan	Air flow rate - 50Hz	Cooling	At high/medium/low fan speed	m³/min	8.7/7.5/6.5	9.0/7.5/6.5	9.5/8.0/7.0	15.0/12.5/11.0	15.2/12.5/11.0	21.0/18.0/15.0	23.0/19.5/16.0	32.0/27.0/23.0	36.0/31.5/26.0	39.0/34.0/28.0
		Heating	At high/medium/low fan speed	m³/min	8.7/7.5/6.5	9.0/7.5/6.5	9.5/8.0/7.0	15.0/12.5/11.0	15.2/12.5/11.0	21.0/18.0/15.0	23.0/19.5/16.0	32.0/27.0/23.0	36.0/31.5/26.0	42.5/34.0/28.0
Air filter	Type	Resin net												
		External static pressure - 50Hz	Factory set / High	Pa	30/150			40/150			50/150			
Sound power level	Cooling	At high fan speed	dBA	54		55	60	59	61	64				
		At high/medium/low fan speed	dBA	29.5/28.0/25.0	30.0/28.0/25.0	31.0/29.0/26.0	35.0/32.0/29.0	33.0/30.0/27.0	35.0/32.0/29.0	36.0/34.0/31.0	39.0/36.0/33.0	41.5/38.0/34.0		
Sound pressure level	Heating	At high/medium/low fan speed	dBA	31.5/29.0/26.0	32.0/29.0/26.0	33.0/30.0/27.0	37.0/34.0/29.0	35.0/32.0/28.0	37.0/34.0/30.0	37.0/34.0/31.0	40.0/37.0/33.0	42.0/38.5/34.0		
		At high/medium/low fan speed	dBA	31.5/29.0/26.0	32.0/29.0/26.0	33.0/30.0/27.0	37.0/34.0/29.0	35.0/32.0/28.0	37.0/34.0/30.0	37.0/34.0/31.0	40.0/37.0/33.0	42.0/38.5/34.0		
Refrigerant	Type/GWP	R-32/675.0												
Piping connections	Liquid	OD	mm	6.35				9.52						
	Gas	OD	mm	9.52				12.70						
Drain	VP20 (I.D. 20/O.D. 26), drain height 625 mm													
	Power supply	Phase/Frequency/Voltage	Hz/V	1~/50/60/220-240/220										
Current - 50Hz	Maximum fuse amps (MFA)	A	6											
Control systems	Infrared remote control	BRC4C65 / BRC4C66 (1)												
		Wired remote control	BRC1H52W/S/K											

(1) Must be combined with Madoka wired remote controller | Contains fluorinated greenhouse gases

# Concealed ceiling unit with high ESP


Ideal for large sized spaces ESP up to 270 Pa

- Optimised for R-32 refrigerant
- Possibility to change ESP via wired remote control allows optimisation of the supply air volume
- High external static pressure up to 270Pa facilitates extensive duct and grille network
- Discretely concealed in the wall: only the suction and discharge grilles are visible
- Fresh air intake integrated in the same system thus reducing installation cost as no additional ventilation device is required (50-125 class)



\* Brings in up to 10% of fresh air into the room

- Flexible installation, as the air suction direction can be altered from rear to bottom suction (50-125 class)





### Automatic Airflow Adjustment function


Automatically selects the most appropriate fan curve to achieve the units' nominal air flow within ±10%

#### Why?

After installation the real ducting will frequently differ from the initially calculated air flow resistance \* the real air flow may be much lower or higher than nominal, leading to a lack of capacity or uncomfortable air temperature. Automatic Airflow Adjustment function will adapt the unit's fan speed to any ducting automatically (10 or more fan curves are available on every model), making installation much faster



- Standard built-in drain pump with 625mm lift increases flexibility and installation speed (optional for 200-250)



- High external static pressure up to 270Pa facilitates extensive duct and grille network
- Large capacity unit: up to 31.5 kW heating capacity

More details and final information can be found by scanning or clicking the QR codes.



Indoor Unit		FXMA	50A	63A	80A	100A	125A	200A	250A		
Cooling capacity	Total capacity	kW	5.6	7.1	9.0	11.2	14.0	22.4	28.0		
	At high fan speed	kW									
Heating capacity	Total capacity	kW	6.3	8.0	10.0	12.5	16.0	25.0	31.5		
	At high fan speed	kW									
Power input - 50Hz	Cooling	kW	0.125	0.140	0.198	0.191	0.254	0.54	0.65		
	Heating	kW	0.125	0.140	0.198	0.191	0.254	0.54	0.65		
Required ceiling void >	mm	350									
Dimensions	Unit	mm	300x1,000x700			300x1,400x700		470x1,572x1,143			
	HeightxWidthxDepth	mm	300x1,000x700			300x1,400x700		470x1,572x1,143			
Weight	Unit	kg	35		46	105	115				
Fan	Air flow rate - 50Hz	Cooling	H/M/L fan speed	m³/min	18.0/16.5/15.0	19.5/17.5/16.0	25.0/22.5/20.0	32.0/27.0/23.0	36.0/30.0/26.0	62.0/48.0/41.0	74.0/64.0/52.0
		Heating	H/M/L fan speed	m³/min	18.0/16.5/15.0	19.5/17.5/16.0	25.0/22.5/20.0	32.0/27.0/23.0	36.0/30.0/26.0	62.0/48.0/41.0	74.0/64.0/52.0
Air filter	Type	Resin net									
		External static pressure - 50Hz	Factory set / High	Pa	200/100			250/150			
Sound power level	Cooling	H/M/L fan speed	dBA	61.0/60.0/58.0	64.0/61.0/59.0	67.0/64.0/62.0	65.0/61.0/56.0	70.0/66.0/62.0	75.0/74.0/72.0	76.0/75.0/73.0	
		Heating	H/M/L fan speed	dBA	62.0/61.0/59.0	65.0/62.0/60.0	68.0/65.0/63.0	66.0/62.0/57.0	71.0/67.0/63.0	75.0/74.0/72.0	76.0/75.0/73.0
Sound pressure level	Cooling	H/M/L fan speed	dBA	41.0/39.0/37.0	42.0/40.0/38.0	43.0/41.0/39.0	44.0/42.0/40.0	48.0/46.5/45.0			
		Heating	H/M/L fan speed	dBA	41.0/39.0/37.0	42.0/40.0/38.0	43.0/41.0/39.0	44.0/42.0/40.0	48.0/46.5/45.0		
Refrigerant	Type/GWP	R-32/675									
Piping connections	Liquid	Type/OD	mm	Flare connection 6.35			Flare connection 9.52				
	Gas	Type/OD	mm	Flare connection 12.7			Flare connection 15.9				
Drain	VP25 (I.D. 25/O.D. 32)										
	Power supply	Phase/Frequency/Voltage	Hz/V	1~/50/60/220-240/220					1~/50/60/220-230		
Current - 50Hz	Maximum fuse amps (MFA)	A	6								
Control systems	Infrared remote control	BRC4C65									
		Wired remote control	BRC1H52W/S/K								

Contains fluorinated greenhouse gases

# Wall mounted unit

For rooms with no false ceilings nor free floor space

- › Optimised design for R-32 refrigerant
- › Flat, stylish front panel blends easily within any interior décor and is easier to clean
- › Can easily be installed in both new and refurbishment projects
- › The air is comfortably spread up- and downwards thanks to 5 different discharge angles that can be programmed via the remote control
- › Maintenance operations can be performed easily from the front of the unit



BRC1H52W, BRP069C51

FXAA-A

3 fan speeds available!

More details and final information can be found by scanning or clicking the QR codes.




Indoor Unit		FXAA	15A	20A	25A	32A	40A	50A	63A
Cooling capacity	Total capacity	kW							
	At high fan speed	1.7	2.2	2.8	3.6	4.5	5.6	7.1	
Heating capacity	Total capacity	kW							
	At high fan speed	1.9	2.5	3.2	4.0	5.0	6.3	8.0	
Power input – 50Hz	Cooling	kW							
	At high fan speed	0.017	0.019	0.028	0.030	0.025	0.033	0.050	
Heating	At high fan speed	0.025	0.029	0.034	0.035	0.030	0.039	0.060	
	Unit	mm							
Dimensions	HeightxWidthxDepth	290x795x266							
Weight	Unit	kg							
		12							
Fan	Air flow rate – 50Hz	m³/min							
	Cooling	7.1/6.8/6.5	7.9/7.2/6.5	8.3/7.4/6.5	9.4/8.0/6.5	12.2/11.0/9.8	14.2/12.6/10.9	18.2/15.5/12.9	
Heating	At high/medium/low fan speed								
	At high/medium/low fan speed	7.8/7.1/6.5	8.6/7.5/6.5	9.0/7.7/6.5	9.9/8.2/6.5	12.2/11.0/9.8	15.2/13.7/12.1	18.7/16.4/14.1	
Air filter	Type	Removable / washable							
Sound power level	Cooling	dB(A)							
	At high fan speed	51.0	52.0	53.0	55.0	58.0	63.0		
Sound pressure level	Cooling	dB(A)							
	At high/medium/low fan speed	32.0/30.5/28.5	33.0/31.0/28.5	35.0/32.0/28.5	37.5/33.0/28.5	37.0/35.5/33.5	41.0/38.5/35.5	46.5/42.5/38.5	
Heating	At high/medium/low fan speed	33.0/31.0/28.5	34.0/31.5/28.5	36.0/32.5/28.5	38.5/33.5/28.5	38.0/36.0/33.5	42.0/39.0/35.5	47.0/43.0/38.5	
	Type/GWP	R-32/675.0							
Piping connections	Liquid	mm							
	OD	6.35							
Gas	OD	mm							
		9.52							
Drain		mm							
		VP13 (I.D. 15/O.D. 18)							
Power supply	Phase/Frequency/Voltage	Hz/V							
		1~/50 /220-240							
Current – 50Hz	Maximum fuse amps (MFA)	A							
		6							
Control systems	Infrared remote control	BRC7EA630 (1)							
	Wired remote control	BRC1H52W/S/K							

(1) Must be combined with Madoka wired remote controller | Contains fluorinated greenhouse gases

# Ceiling suspended unit

For wide rooms with no false ceilings nor free floor space


- › Optimised for R-32 refrigerant
- › Ideal for comfortable air flow in wide rooms thanks to Coanda effect: up to 100° discharge angle



- › Even rooms with ceilings up to 3.8m can be heated up or cooled down very easily without capacity loss
- › Can easily be installed in both new and refurbishment projects
- › Can easily be mounted in corners and narrow spaces, as it only needs 30mm lateral service space



- › Fresh air intake integrated in the same system thus reducing installation cost as no additional ventilation device is required



\* Brings in up to 10% of fresh air into the room

- › Stylish unit blends easily with any interior. The flaps close entirely when the unit is not operating and there are no air intake grilles visible

More details and final information can be found by scanning or clicking the QR codes.



Indoor Unit		FXHA	32A	50A	63A	100A
Cooling capacity	Total capacity	kW				
	At high fan speed	3.6	5.6	7.1	11.2	
Heating capacity	Nom.	kW				
	At high fan speed	4.0	6.3	8.0	12.5	
Power input – 50Hz	Cooling	kW				
	At high fan speed	0.033	0.037	0.051	0.086	
Heating	At high fan speed	0.033	0.037	0.051	0.086	
	Unit	mm				
Dimensions	HeightxWidthxDepth	235x960x690				
Weight	Unit	kg				
		28				
Casing	Material	Resin, sheet metal				
Fan	Air flow rate – 50Hz	m³/min				
	Cooling	12.5/11.0/10.0	16.0/14.0/12.5	17.5/15.0/13.0	27.0/22.0/19.0	
Heating	At high/medium/low fan speed					
	At high/medium/low fan speed	12.5/11.0/10.0	16.0/14.0/12.5	17.5/15.0/13.0	27.0/22.0/19.0	
Air filter	Type	Resin net with mold resistance				
Sound power level	Cooling	dB(A)				
	At high/medium/low fan speed	54.0/52.0/49.0	54.0/52.0/50.0	55.0/53.0/52.0	62.0/55.0/52.0	
Sound pressure level	Cooling	dB(A)				
	At high/medium/low fan speed	36.0/34.0/31.0	36.5/34.5/33.0	37.0/35.0/34.0	44.0/37.0/34.0	
Heating	At high/medium/low fan speed	36.0/34.0/31.0	36.5/34.5/33.0	37.0/35.0/34.0	44.0/37.0/34.0	
	Type/GWP	R-32/675				
Piping connections	Liquid	mm				
	OD	6.4				
Gas	OD	mm				
		9.52	12.7	15.9		
Drain		mm				
		VP20				
Power supply	Phase/Frequency/Voltage	Hz/V				
		1~/50/60/220-240/220				
Current – 50Hz	Maximum fuse amps (MFA)	A				
		6				
Control systems	Infrared remote control	BRC7GA53-9				
	Wired remote control	BRC1H52W/S/K				

Contains fluorinated greenhouse gases

# 4-way blow ceiling suspended unit

Unique Daikin unit for high rooms with no false ceilings nor free floor space

- › Optimised for R-32 refrigerant
- › Even rooms with ceilings up to 3.5m can be heated up or cooled down very easily without capacity loss
- › Can easily be installed in both new and refurbishment projects
- › Individual flap control: flexibility to suit every room layout without changing the location of the unit!




FXUA-A




BRC1H52W, BRP069C51



- › Stylish unit blends easily with any interior. The flaps close entirely when the unit is not operating and there are no air intake grilles visible
- › Optimum comfort guaranteed with automatic air flow adjustment to the required load
- › 5 different discharge angles between 0 and 60° can be programmed via the remote control



- › Standard drain pump with 720mm lift increases flexibility and installation speed



More details and final information can be found by scanning or clicking the QR codes.



		NEW capacity range									
Indoor Unit		FXUA		50A		71A		100A			
Cooling capacity	Total capacity			5.6		8.0		11.2			
	At high fan speed										
Heating capacity	Total capacity			6.3		9.0		12.5			
	At high fan speed										
Power input – 50Hz	Cooling			0.029		0.055		0.117			
	At high fan speed										
Dimensions	Unit	HeightxWidthxDepth		mm		198x950x950					
	Weight	Unit		kg		27		28			
Casing	Material				Resin						
Fan	Type				Turbo fan						
	Quantity				1						
Air flow rate – 50Hz	Cooling	At high/medium/low fan speed		m <sup>3</sup> /min		17.0/14.5/13.0		22.5/18.5/16.0		31.0/25.5/21.0	
		At high/medium/low fan speed		m <sup>3</sup> /min		17.0/14.5/13.0		22.5/18.5/16.0		31.0/25.5/21.0	
Sound power level	Cooling	At high/medium/low fan speed		dBA		55.0/53.0/51.0		58.0/56.0/54.0		65.0/62.0/58.0	
		At high/medium/low fan speed		dBA		55.0/53.0/51.0		58.0/56.0/54.0		65.0/62.0/58.0	
Sound pressure level	Cooling	At high/medium/low fan speed		dBA		37.0/35.0/33.0		40.0/38.0/36.0		47.0/44.0/40.0	
		At high/medium/low fan speed		dBA		37.0/35.0/33.0		40.0/38.0/36.0		47.0/44.0/40.0	
Refrigerant	Type/GWP				R-32/675						
Piping connections	Liquid	OD		mm		6.4		9.52			
		OD		mm		12.7		15.9			
Drain					VP20						
Power supply	Phase/Frequency/Voltage		Hz/V		1~/50/60/220-240/220						
Current – 50Hz	Maximum fuse amps (MFA)		A		6						
Control systems	Infrared remote control				BRC7CB58 / BRC7CB59						
	Wired remote control				BRC1H52W/S/K						

Contains fluorinated greenhouse gases



Outdoor units

		VRV Heat Recovery	
		REVA8-20A REMA5A	2 module systems
Kits	Heater tape kit – Optional electrical heater to guarantee trouble-free operation in extremely cold and humid climates (one per outdoor unit needed)	5/8-12: EKBPH012T7A 14-20: EKBPH020T7A	
	Multi-module connection kit (obligatory) – Connects multiple modules into a single refrigerant system		BHFQ23P907A

BSSV Boxes

		VRV Heat Recovery
		BS-A14AV1B
	EKBSDCCK – Duct connection: To connect extraction of BSSV boxes in serial	•
	EKBSJK – Joint kit for branch selector (BS) boxes: To couple 2 BS box branches to connect larger capacity indoor units	•
	K-KDU303KVE – Drain pump kit	•

		Ceiling mounted cassette units		Concealed ceiling units (duct units)			Ceiling suspended units		Wall mounted units
		Round flow (800x800)	4-way (600x600)	Slim	Medium ESP	High ESP	1-way blow	4-way blow	
		FXFA-A	FXZA-A	FXDA-A	FXSA-A	FXMA-A	FXHA-A	FXUA-A	FXAA-A
Panels	Decoration panel (obligatory for cassette units, optional for others, rear panel for FXLQ)	Standard panels: BYCQ140E (white) / BYCQ140EW (full white)(3) / BYCQ140EB (black) Auto cleaning (5)(6): BYCQ140EGF (white) / BYCQ140EGFB (black) Designer panels: BYCQ140EP (white) / BYCQ140EPB (black)	R-32 model: BYFQ60C4W1W (white panel) (19) BYFQ60C4W1S (grey panel) (19) BYFQ60B3W1 (standard panel) (20)						
	Panel spacer for reducing required installation height		KDBQ44B60 (Standard panel)						
	Sealing kit for 3- or 2-directional air discharge	KDBHQ56B140 (7)	BDBHQ44C60 (white & grey panel)						KDBHP49B140 + KDBTP49B140
Individual control systems	Sensor kit	BRYQ140B (white panels) BRYQ140BB (black panels) BRYQ140C (white designer panel) BRYQ140CB (black designer panel)	R-32 models: BRYQ60A3W (white) BRYQ60A3S (grey)					BRE49B2F	
	Infrared remote control (incl. receiver)	BRC7FA532F (white panels) (7)(15) BRC7FA532FB (black panels) (7)(15) BRC7FB532F (white designer panel) (7)(15) BRC7FB532FB (black designer panel) (7)(15)	BRC7F530W (9) (10) (white panel) BRC7F530S (9) (10) (grey panel) BRC7EB530W (9) (10) (standard panel)	BRC4C65	BRC4C65	BRC4C65	BRC7GA53-9	BRC7C58	BRC7EA630
Centralised control systems	BRP069C51 – Onecta app	•	•	•	•	•	•	•	•
	Madoka BRC1H52W (White) / BRC1H52S (Silver) / BRC1H52K (Black) User-friendly wired remote controller with premium design	• (mandatory)	• (mandatory)	• (mandatory)	• (mandatory)	• (mandatory)	• (mandatory)	• (mandatory)	• (mandatory)
	DCC601A51 – intelligent Tablet Controller	•	•	•	•	•	•	•	•
	DCS601C51 (I2) – intelligent Touch Controller	•	•	•	•	•	•	•	•
	DCS302C51 (I2) – Central remote controller	•	•	•	•	•	•	•	•
Building Management System & Standard protocol interfaces	DCS301B51 (I2) (I3) – Unified ON/OFF controller	•	•	•	•	•	•	•	•
	RTD-NET – Modbus interface for monitoring and control	•	•	•	•	•	•	•	•
	RTD-10 – Modbus interface for infrastructure cooling	•	•	•	•	•	•	•	•
	RTD-20 – Modbus interface for retail	•	•	•	•	•	•	•	•
	RTD-HO – Modbus interface for hotel	•	•	•	•	•	•	•	•
	KLIC-DI – KNX Interface	•	•	•	•	•	•	•	•
	DCM601A51 – intelligent Touch Manager	•	•	•	•	•	•	•	•
	EKMBDXB – Modbus interface	•	•	•	•	•	•	•	•
	DCM010A51 – Daikin PMS interface	•	•	•	•	•	•	•	•
	DMS502A51 – BACnet Interface	•	•	•	•	•	•	•	•
DMS504B51 – LonWorks Interface	•	•	•	•	•	•	•	•	
Filters	Replacement long life filter, non-woven type	KAF5511D160	KAF441C60			200~250: BAFL502A250 (20)	32: KAFP501A56 50~63: KAFP501A80 100: KAFP501A160	KAFP551K160	
	Auto cleaning filter	see decoration panel		15-32: BAE20A62 40-50: BAE20A82 63: BAE20A102					
Wiring and sensors	KRCS – External wired temperature sensor	KRCS01-7B	KRCS01-8B	KRCS01-8B	KRCS01-8B	KRCS01-8B	KRCS01-8B	KRCS01-8B	KRCS01-8B
	K.RSS – External wireless temperature sensor	SB.K.RSS_RFC (EKEWTSC-2 + K.RSS)	SB.K.RSS_FDA (EKEWTSC-1 + K.RSS)	SB.K.RSS_FDA (EKEWTSC-1 + K.RSS)	K.RSS_FDA (EKEWTSC-1 + K.RSS)	SB.K.RSS_FDA (EKEWTSC-1 + K.RSS)	•	SB.K.RSS_FDA (EKEWTSC-1 + K.RSS)	SB.K.RSS_FDA (EKEWTSC-1 + K.RSS)
Adapters	Adapter with 2 output signals (Compressor / Error, Fan output)	KRP1BA58 (2)(7)	ERP02A50 (2)				KRP1BA58		
	Adapter with 4 output signals (Compressor / Error, Fan, Aux. heater, Humidifier output)	EKRPI1C12 (2)(7)	EKRPI1C14 (2)	ERP02A50 (2)	EKRPI1C14 (2)	EKRPI1C14 (2)		EKRPI1C14 (2)	ERP02A50 (2)
	Adapter for centralised external monitoring/control via dry contacts and setpoint control via 0-140Ω	KRP4A53 (2)(7)	KRP4A53 (2)	KRP4A54-9 (2)	KRP4A52(2)	50~125: KRP4A52 200~250: KRP4A51	KRP4A52 (2)	KRP4A53 (2)	KRP4A51 (2)
	Adapter for external central monitoring/control (controls 1 entire system)		KRP2A52	KRP2A53 (2)	KRP2A51(2)	KRP2A51	KRP2A62		KRP2A61(2)
	Adapter for keypad and/or window contact connection (2)(11)	BRP7A53	BRP7A53 (2)	BRP7A54	BRP7A51	BRP7A51	BRP7A52 (2)	BRP7A53	BRP7A51 (2)
	Adapter for multi-tenant applications (24 VAC PCB power supply interface)			DTA114A61					
	External control adapter for outdoor unit (installation on indoor unit)			DTA104A53	DTA104A61 (2)	DTA104A61 (2)	DTA104A61		DTA104A51(2) / DTA104A61(2)
	Installation box / Mounting plate for adapter PCBs (For units where there is no space in the switchbox)	KRP1H98A (7) KRP1BC101	KRP1BB101 KRP1BC101	KRP1BB101	KRP1BC101	KRP1BC101	KRP1D93A/ KRP4B93	KRP1B97	KRP4A93
	Wiring kit for Remote ON/OFF or Forced OFF	Standard	Standard	Standard	Standard	Standard	standard	standard	Standard
	Relay PCB for output signal of refrigerant sensor	ERP01A51 (2)	ERP01A50 (2)	ERP01A51 (2)	ERP01A50 (2)	ERP01A50	ERP01A51 (2)	ERP01A51 (2)	ERP01A51 (2)
Others	Drain pump kit	Standard	Standard	Standard	Standard	200~250: BDU510B250VVM	32-50-63: KDU50R63 100: KDU50R160		K-KDU572KVE
	Fresh air intake kit (direct installation type)	KDDP55C160-1 + KDDP55D160-2 (7)(8)	KDDQ44XA60				KDDQ50A140		
	Air discharge adapter for round duct				15~32: KDAP25A36A 40~50: KDAP25A56A 63~80: KDAP25A71A 100~125: KDAP25A140A 140: -	50~80: KDAJ25K71 100~125: KDAJ25K140 200~250: -			
	L-type piping kit						32: KHFP5M35 50~63: KHFP5N63 100: KHFP5N160		

(1) Pump station is necessary for this option  
 (2) Installation box is necessary for these adapters  
 (3) The BYCQ140EW has white insulation. Be informed that formation of dirt on white insulation is visibly stronger and that it is consequently not advised to install the BYCQ140EW decoration panel in environments exposed to concentrations of dirt\*  
 (4) Not recommended because of the limitation of the functions

(5) To be able to control the BYCQ140EGF(B) the controller BRCIE or BRCIH\* is needed  
 (6) The BYCQ140EGF(B) is not compatible with Multi and Split Non-Inverter Outdoor units  
 (7) Option not available in combination with BYCQ140EGF(B)  
 (8) Both parts of the fresh air intake are needed for each unit  
 (9) Cannot be combined with sensor kit  
 (10) Independently controllable flaps function not available

(11) Only possible in combination with BRCIH\* / BRCIE\*  
 (12) When fixing box is required, use KJB212A, KJB311A or KJB411A depending on the size of the controller  
 (13) Option KEK26-1A (Noise filter) is required when installing DCS301B51  
 (14) Wire harness EKEWTSC is necessary  
 (15) The active airflow circulation function is not available for this controller.  
 (16) Up to 2 adaptor PCBs can be installed per installation box

(17) Only one installation box can be installed per indoor unit  
 (18) VRV R-32 indoor units cannot be connected to this controller  
 (19) The BYFQ60C4\* R-32 panels can be connected to R-410A indoor units with wire harness EKRS22  
 (20) Wire harness EKRS23 is necessary



# Technical

drawings

Technical drawings 36


---

Outdoor units 36

BSSV box 38

Indoor units 39

REYA8-12A / REMA5A




NOTES

- Detail A and detail B indicate the dimensions after fixing the attached piping.
- Items 4 – 10: Knockout hole.
- Gas pipe
  - RYYQ8U, RYM08U, RXYQ8U, RXYQ08U, RXYTQ8U Ø 19.1 brazing connection
  - RYYQ10U, RYM010U, RXYQ10U, RXYQ010U Ø 22.2 brazing connection
  - REMQ5U, REMA5A, REYQ8-12U, REYA8-12A Ø 25.4 brazing connection
  - RYYQ12U, RYM012U, RXYQ12U, RXYQ012U Ø 28.6 brazing connection
- Liquid pipe
  - RYYQ8-10U, RYM08-10U, RXYQ8-10U, RXYQ08-10U, Ø 9.5 brazing connection
  - REMQ5U, REMA5A, REYQ8-12U, REYA8-12A, RXYTQ8U Ø 12.7 brazing connection
  - RYYQ12U, RYM012U, RXYQ12U, RXYQ012U Ø 19.1 brazing connection
  - RYM08-10U Ø 22.2 brazing connection
  - RYM012U Ø 22.2 brazing connection
- High pressure/low pressure gas pipe
  - REMQ5U, REMA5A, REYQ8-12U, REYA8-12A Ø 19.1 brazing connection

No.	Part name	Remark
1	Liquid pipe connection port	See note -3.
2	Gas pipe connection port	See note -3.
3	Equalising pipe connection port High pressure/low pressure gas pipe	See note -3.
4	Power cord routing hole (side)	Ø65
5	Power cord routing hole (front)	Ø80
6	Power cord routing hole (front)	Ø65
7	Power cord routing hole (front)	Ø27
8	Power cord routing hole (bottom)	Ø65
9	Pipe routing hole (front)	
10	Pipe routing hole (bottom)	
11	Grounding terminal	Inside of the switch box (M8)

2D119001A

REYA14-20A




NOTES

- Detail A and detail B indicate the dimensions after fixing the attached piping.
- Items 4 – 10: Knockout hole.
- Gas pipe
  - RXYTQ10U Ø 22.2 brazing connection
  - REYQ14-20U, REYA14-20A Ø 25.4 brazing connection
  - RYYQ14-20U, RYM014-20U, RXYQ14-20U, RXYQ014-20U, RXYTQ12-16U Ø 28.6 brazing connection
- Liquid pipe
  - RXYTQ10U Ø 9.5 brazing connection
  - RYYQ14-16U, RYM014-16U, RXYQ14-16U, RXYQ014-16U, REYQ14-20U, REYA14-20A, RXYTQ12-16U Ø 12.7 brazing connection
  - RYYQ18-20U, RYM018-20U, RXYQ18-20U, RXYQ018-20U Ø 15.9 brazing connection
- Equalising pipe
  - RYM014-16U Ø 22.2 brazing connection
  - RYM018-20U Ø 28.6 brazing connection
- High pressure/low pressure gas pipe
  - REYQ14-20U, REYA14-20A Ø 19.1 brazing connection

No.	Part name	Remark
1	Liquid pipe connection port	See note 3.
2	Gas pipe connection port	See note 3.
3	Equalising pipe connection port High pressure/low pressure gas pipe	See note 3.
4	Power cord routing hole (side)	Ø65
5	Power cord routing hole (front)	Ø80
6	Power cord routing hole (front)	Ø65
7	Power cord routing hole (front)	Ø27
8	Power cord routing hole (bottom)	Ø65
9	Pipe routing hole (front)	
10	Pipe routing hole (bottom)	
11	Grounding terminal	Inside of the switch box (M8)

2D119091A

REYA-A / REMA-A




NOTES

- Height of the walls in case of patterns 1 and 2:
  - Front: 1500mm
  - Suction side: 500mm
  - Side: height unrestricted


The installation space shown on this drawing is based on cooling operation at 35°C (outdoor temperature).

When the design outdoor ambient temperature exceeds 35°C or the load exceeds maximum ability of much generation load of heat in all outdoor unit, make sure the suction-side space is broader than the space shown on this drawing.
- If the walls are higher than mentioned above, then additional service space is needed:
  - suction side: service space + h1/2
  - front side: service space + h2/2
- When installing the units, select the pattern that best fits the available space.
- Always keep in mind to leave sufficient space for a person to pass between unit and wall and for the air to circulate freely.
- If more units are to be installed than are catered for in the above patterns, your layout should take into account of the possibility of short circuits.
- Provide sufficient space at the front to connect refrigerant piping (comfortably).




3D118467A

BS-A14AV1B




3D139837

FXFA-A WITH STANDARD PANEL



2D121655D

FXFA-A WITH AUTO CLEANING PANEL









2D121658D



**FXDA10-32A**

Service space of installation box for adaptor PCB.



**NOTES**







- In case of bottom suction, mount the chamber cover to the backside of the unit. For more information, refer to the installation manual.
- In case of rear suction, mount the chamber cover to the bottom side of the unit. For more information, refer to the installation manual.
- The unit nameplate is located on the control box cover.
- Mount the air filter at the suction side. Use an air filter with a dust collecting efficiency of at least 50% (measured by gravimetric analysis). When a duct is connected at the suction side, it is not possible to mount an air filter.

Item	Description
1	Liquid pipe connection -ø6.35- Flare connection
2	Gas pipe connection -ø9.52- Flare connection
3	Drain pipe connection Outside diameter: ø26 Inside diameter: ø20
4	Drain hose (accessory) Inside diameter: ø25
5	Control box
6	Transmission wiring connection
7	Power supply connection
8	Suspension bracket
9	Inspection door
10	Drain socket
11	Air filter (accessory)
12	Heat exchanger
13	Turbo fan
14	Fan motor
15	Fan housing
16	Drain pump
17	Float switch
18	Electronic expansion valve

**2D126395**

**FXDA40-50A**

Service space of installation box for adaptor PCB.



**NOTES**







- In case of bottom suction, mount the chamber cover to the backside of the unit. For more information, refer to the installation manual.
- In case of rear suction, mount the chamber cover to the bottom side of the unit. For more information, refer to the installation manual.
- The unit nameplate is located on the control box cover.
- Mount the air filter at the suction side. Use an air filter with a dust collecting efficiency of at least 50% (measured by gravimetric analysis). When a duct is connected at the suction side, it is not possible to mount an air filter.

Item	Description
1	Liquid pipe connection -ø6.35- Flare connection
2	Gas pipe connection -ø12.70- Flare connection
3	Drain pipe connection Outside diameter: ø26 Inside diameter: ø20
4	Drain hose (accessory) Inside diameter: ø25
5	Control box
6	Transmission wiring connection
7	Power supply connection
8	Suspension bracket
9	Inspection door
10	Drain socket
11	Air filter (accessory)
12	Heat exchanger
13	Turbo fan
14	Fan motor
15	Fan housing
16	Drain pump
17	Float switch
18	Electronic expansion valve

**2D126677**

**FXDA63A**

Service space of installation box for adaptor PCB.




**NOTES**

- In case of bottom suction, mount the chamber cover to the backside of the unit. For more information, refer to the installation manual.
- In case of rear suction, mount the chamber cover to the bottom side of the unit. For more information, refer to the installation manual.
- The unit nameplate is located on the control box cover.
- Mount the air filter at the suction side. Use an air filter with a dust collecting efficiency of at least 50% (measured by gravimetric analysis). When a duct is connected at the suction side, it is not possible to mount an air filter.

Item	Description
1	Liquid pipe connection -ø6.35- Flare connection
2	Gas pipe connection -ø12.70- Flare connection
3	Drain pipe connection Outside diameter: ø26 Inside diameter: ø20
4	Drain hose (accessory) Inside diameter: ø25
5	Control box
6	Transmission wiring connection
7	Power supply connection
8	Suspension bracket
9	Inspection door
10	Drain socket
11	Air filter (accessory)
12	Heat exchanger
13	Turbo fan
14	Fan motor
15	Fan housing
16	Drain pump
17	Float switch
18	Electronic expansion valve

**2D126592**

**FXDA10A**




**NOTES**

- The fan characteristics shown are in "fan only" mode.
- ESP: External Static Pressure
- The air flow is factory-set to 'standard'. It is possible to switch between 'standard ESP' and 'high ESP' by remote controller setting.

**3D129552**


**FXDA15A**



- NOTES**
1. The fan characteristics shown are in "fan only" mode.
  2. ESP: External Static Pressure
  3. The air flow is factory-set to 'standard'. It is possible to switch between 'standard ESP' and 'high ESP' by remote controller setting.

**3D129553**


**FXDA20-25A**



- NOTES**
1. The remote controller can be used to switch between 'high' and 'low'.
  2. The air flow is factory-set to 'standard'. It is possible to switch between 'standard ESP' and 'high ESP' by remote controller setting.

**3D086736B**


**FXDA32A**



- NOTES**
1. The remote controller can be used to switch between 'high' and 'low'.
  2. The air flow is factory-set to 'standard'. It is possible to switch between 'standard ESP' and 'high ESP' by remote controller setting.

**3D081425C**


**FXDA40A**



- NOTES**
1. The remote controller can be used to switch between 'high' and 'low'.
  2. The air flow is factory-set to 'standard'. It is possible to switch between 'standard ESP' and 'high ESP' by remote controller setting.

**3D081426C**


**FXDA50A**



- NOTES**
1. The remote controller can be used to switch between 'high' and 'low'.
  2. The air flow is factory-set to 'standard'. It is possible to switch between 'standard ESP' and 'high ESP' by remote controller setting.

**3D081427C**


**FXDA63A**



- NOTES**
1. The remote controller can be used to switch between 'high' and 'low'.
  2. The air flow is factory-set to 'standard'. It is possible to switch between 'standard ESP' and 'high ESP' by remote controller setting.

**3D081429C**

**FXSA15-32A**




- NOTES**
1. When installing optional accessories, refer to their respective documentation.
  2. The ceiling depth varies according to the documentation of the specific system.
  3. In case of bottom suction, mount the chamber cover to the backside of the unit. For more information, refer to the installation manual.
  4. In case of rear suction, mount the chamber cover to the bottom side of the unit. For more information, refer to the installation manual.

**3D128686A**

Item	Name	Description
KA	Liquid pipe connection port	Ø6.35- flared connection
KB	Gas pipe connection port	Ø9.52- flared connection
KC	Drain pipe connection	VP20 (OD Ø26, ID Ø20)
KD	Wiring connection	/
KE	Power supply connection	/
KF	Drain outlet	VP20 (OD Ø26, ID Ø20)
KG	Air filter	/
KH	Air suction side	/
KJ	Air discharge side	/
KK	Nameplate	/

**FXSA40-50A**




- NOTES**
1. When installing optional accessories, refer to their respective documentation.
  2. The ceiling depth varies according to the documentation of the specific system.
  3. In case of bottom suction, mount the chamber cover to the backside of the unit. For more information, refer to the installation manual.
  4. In case of rear suction, mount the chamber cover to the bottom side of the unit. For more information, refer to the installation manual.

**3D128715A**

Item	Name	Description
KA	Liquid pipe connection port	Ø6.35- flared connection
KB	Gas pipe connection port	Ø12.70- flared connection
KC	Drain pipe connection	VP20 (OD Ø26, ID Ø20)
KD	Wiring connection	/
KE	Power supply connection	/
KF	Drain outlet	VP20 (OD Ø26, ID Ø20)
KG	Air filter	/
KH	Air suction side	/
KJ	Air discharge side	/
KK	Nameplate	/

**FXSA63-80A**




Item	Name	Description
KA	Liquid pipe connection port	Ø6.35 flared connection
KB	Gas pipe connection port	Ø12.70 flared connection
KC	Drain pipe connection	VP20 (OD Ø26, ID Ø20)
KD	Wiring connection	/
KE	Power supply connection	/
KF	Drain outlet	VP20 (OD Ø26, ID Ø20)
KG	Air filter	/
KH	Air suction side	/
KJ	Air discharge side	/
KK	Nameplate	/

**3D128716A**

**NOTES**

- When installing optional accessories, refer to their respective documentation.
- The ceiling depth varies according to the documentation of the specific system.
- In case of bottom suction, mount the chamber cover to the backside of the unit. For more information, refer to the installation manual.
- In case of rear suction, mount the chamber cover to the bottom side of the unit. For more information, refer to the installation manual.

**FXSA100-125A**




Item	Name	Description
KA	Liquid pipe connection port	Ø9.52 flared connection
KB	Gas pipe connection port	Ø15.90 flared connection
KC	Drain pipe connection	VP20 (OD Ø26, ID Ø20)
KD	Wiring connection	/
KE	Power supply connection	/
KF	Drain outlet	VP20 (OD Ø26, ID Ø20)
KG	Air filter	/
KH	Air suction side	/
KJ	Air discharge side	/
KK	Nameplate	/

**3D128719A**

**NOTES**

- When installing optional accessories, refer to their respective documentation.
- The ceiling depth varies according to the documentation of the specific system.
- In case of bottom suction, mount the chamber cover to the backside of the unit. For more information, refer to the installation manual.
- In case of rear suction, mount the chamber cover to the bottom side of the unit. For more information, refer to the installation manual.

**FXSA140A**




Item	Name	Description
KA	Liquid pipe connection port	Ø9.52 flared connection
KB	Gas pipe connection port	Ø15.90 flared connection
KC	Drain pipe connection	VP20 (OD Ø26, ID Ø20)
KD	Wiring connection	/
KE	Power supply connection	/
KF	Drain outlet	VP20 (OD Ø26, ID Ø20)
KG	Air filter	/
KH	Air suction side	/
KJ	Air discharge side	/
KK	Nameplate	/

**3D128720A**

**NOTES**



- When installing optional accessories, refer to their respective documentation.
- The ceiling depth varies according to the documentation of the specific system.
- In case of bottom suction, mount the chamber cover to the backside of the unit. For more information, refer to the installation manual.
- In case of rear suction, mount the chamber cover to the bottom side of the unit. For more information, refer to the installation manual.

**FXSA15A**



Mark	ESP [Pa]
*1	Maximum 150
*2	- 100
*3	Standard 50

Fan characteristics (2)  
Field setting with remote control




1. Upper limit of ESP by air flow auto adjustment  
2. Lower limit of ESP by air flow auto adjustment

**NOTES**

- The fan characteristics shown are in "fan only" mode.
- ESP: External Static Pressure



**3D096999B**

**FXSA20-25A**



Mark	ESP [Pa]
*1	Maximum 150
*2	- 100
*3	Standard 30

Fan characteristics (2)  
Field setting with remote control




1. Upper limit of ESP by air flow auto adjustment  
2. Lower limit of ESP by air flow auto adjustment

**NOTES**

- The fan characteristics shown are in "fan only" mode.
- ESP: External Static Pressure



**3D095680A**

**FXSA32A**



Mark	ESP [Pa]
*1	Maximum 150
*2	- 100
*3	Standard 30

Fan characteristics (2)  
Field setting with remote control




1. Upper limit of ESP by air flow auto adjustment  
2. Lower limit of ESP by air flow auto adjustment

**NOTES**

- The fan characteristics shown are in "fan only" mode.
- ESP: External Static Pressure



**3D095681B**

**FXSA40A**



Mark	ESP [Pa]
*1	Maximum 150
*2	- 100
*3	Standard 30

Fan characteristics (2)  
Field setting with remote control




1. Upper limit of ESP by air flow auto adjustment  
2. Lower limit of ESP by air flow auto adjustment

**NOTES**

- The fan characteristics shown are in "fan only" mode.
- ESP: External Static Pressure


**3D095682B**

**FXSA50A**




**3D095688B**

**FXSA63A**




**3D095690B**

**FXSA80A**






**3D095692B**

**FXSA100A**



**3D095696B**

**FXSA125A**



1. Upper limit of ESP by air flow auto adjustment
2. Lower limit of ESP by air flow auto adjustment




Mark		ESP [Pa]
*1	Maximum	150
*2	-	100
*3	Standard	50

**NOTES**

1. The fan characteristics shown are in "fan only" mode.
2. ESP: External Static Pressure

**3D095697B**

**FXSA140A**



1. Upper limit of ESP by air flow auto adjustment
2. Lower limit of ESP by air flow auto adjustment


Mark		ESP [Pa]
*1	Maximum	150
*2	-	100
*3	Standard	50

**NOTES**

1. The fan characteristics shown are in "fan only" mode.
2. ESP: External Static Pressure

**3D096688B**

**FXMA50-80A**





**NOTES**

1. When installing optional accessories, refer to their respective documentation.T
2. The ceiling depth varies according to the documentation of the specific system.
3. In case of bottom suction, mount the chamber cover to the backside of the unit. For more information, refer to the installation manual.
4. In case of rear suction, mount the chamber cover to the bottom side of the unit. For more information, refer to the installation manual.

Item	Name	Description
KA	Liquid pipe connection port	Ø6.35 Flare connection
KB	Gas pipe connection port	Ø12.70 Flare connection
KC	Drain pipe connection	VP25 (OD Ø32, ID Ø25)
KD	Wiring connexion	/
KE	Power supply connection	/
KF	Drain outlet	VP25 (OD Ø32, ID Ø25)
KG	Air filter	/
KH	Air suction side	/
KJ	Air discharge side	/
KK	Nameplate	/

**3D139544**

**FXMA100-125A**




Item	Name	Description
KA	Liquid pipe connection port	Ø9.52 Flared connection
KB	Gas pipe connection port	Ø15.90 Flared connection
KC	Drain pipe connection	VP25 (OD Ø32, ID Ø25)
KD	Wiring connection	/
KE	Power supply connection	/
KF	Drain outlet	VP25 (OD ø 32, ID ø 25)
KG	Air filter	/
KH	Air suction side	/
KJ	Air discharge side	/
KK	Nameplate	/

**NOTES**

- When installing optional accessories, refer to their respective documentation.
- The ceiling depth varies according to the documentation of the specific system.
- In case of bottom suction, mount the chamber cover to the backside of the unit. For more information, refer to the installation manual.
- In case of rear suction, mount the chamber cover to the bottom side of the unit. For more information, refer to the installation manual.

3D139547

**FXMA200-250A**






**NOTE**

- When installing optional accessories, refer to their respective documentation.
- The unit nameplate is located on the control box cover.

Number	Name	Description
1	Liquid pipe connection port	ø9.5 Flared connection
2	Gas pipe connection port	ø19.1 Brazed connection
3	Electronic component box	/
4	Power supply connection	/
5	Transmission wiring connection	/
6	Metal hanger	M10
7	Air discharge side	/
8	Air suction side	/
9	Accessory pipe	Standard accessory
10	Nameplate	/
11	Drain outlet	1" BSP (female thread) Outside diameter: ø33.3- Inside diameter: ø30.3-
12	Filter chamber	/

3D140557

**FXMA50A**






- Upper limit of ESP by air flow auto adjustment
- Lower limit of ESP by air flow auto adjustment

Mark		ESP [Pa]
①	Maximum	200
②	Standard	100
③	Minimum	50

- NOTES**
- The fan characteristics shown are in "fan only" mode.
  - ESP: External static pressure

4D139872

**FXMA63A**






- Upper limit of ESP by air flow auto adjustment
- Lower limit of ESP by air flow auto adjustment

Mark		ESP [Pa]
①	Maximum	200
②	Standard	100
③	Minimum	50

- NOTES**
- The fan characteristics shown are in "fan only" mode.
  - ESP: External static pressure

4D139877

**FXMA80A**






- ① Upper limit of ESP by air flow auto adjustment
- ② Lower limit of ESP by air flow auto adjustment

Mark		ESP [Pa]
①	Maximum	200
②	Standard	100
③	Minimum	50

**NOTES**  
1. The fan characteristics shown are in "fan only" mode.  
2. ESP: External static pressure

**4D139878**

**FXMA100A**






- ① Upper limit of ESP by air flow auto adjustment
- ② Lower limit of ESP by air flow auto adjustment

Mark		ESP [Pa]
①	Maximum	200
②	Standard	100
③	Minimum	50

**NOTES**  
1. The fan characteristics shown are in "fan only" mode.  
2. ESP: External static pressure

**4D139882**

**FXMA125A**






- ① Upper limit of ESP by air flow auto adjustment
- ② Lower limit of ESP by air flow auto adjustment

Mark		ESP [Pa]
①	Maximum	200
②	Standard	100
③	Minimum	50

**NOTES**  
1. The fan characteristics shown are in "fan only" mode.  
2. ESP: External static pressure

**4D139884**

**FXMA200A**




- ① Upper limit of ESP by air flow auto adjustment
- ② Lower limit of ESP by air flow auto adjustment

Mark		ESP [Pa]
①	Maximum	200
②	Standard	100
③	Minimum	50


**NOTES**  
1. The fan characteristics shown are in "fan only" mode.  
2. ESP: External static pressure

**4D140823**


**FXMA250A**



Field setting with remote control  
Air flow rate range (H)



Air flow auto adjustment




- ① Upper limit of ESP by air flow auto adjustment
- ② Lower limit of ESP by air flow auto adjustment

Mark		ESP [Pa]
①	Maximum	200
②	Standard	100
③	Minimum	50

- NOTES**
- The fan characteristics shown are in "fan only" mode.
  - ESP: External static pressure

**4D140824**


**FXAA15-32A**



- NOTES**
- The ⇨ mark shows the piping direction.
  - Do not place any objects under the indoor unit. In case of high humidity (>80%), clogged drain outlets, or dirty air filters, condensate may drop out.

**3D131071**


**FXAA40-63A**



- NOTES**
- The ⇨ mark shows the piping direction.
  - Do not place any objects under the indoor unit. In case of high humidity (>80%), clogged drain outlets, or dirty air filters, condensate may drop out.

**3D111369**

**FXHA32A**




Item	Name	Description
1	Air discharge grille	
2	Air suction grille	
3	Air filter	
4	Gas pipe connection $\varnothing$ 9.5 flare	
5	Liquid pipe connection $\varnothing$ 6.4 flare	
6	Drain pipe connection	VP20
7	Terminal block with earth terminal Located inside of the unit	M4
8	Metal hanger	
9	Position of knockout hole	Rear side
10	Position of knockout hole	Top
11	Piping intake (right)	Knockout hole
12	Drain piping intake (left)	Knockout hole
13	Drain piping intake (right)	Knockout hole
14	Drain piping intake (left-rear)	Knockout hole
15	Standard location of holes in the wall Piping intake (rear)	$\varnothing$ 100
16	Drain piping intake (top)	$\varnothing$ 60
17	Gas piping intake (top)	$\varnothing$ 36
18	Liquid piping intake (top)	$\varnothing$ 26
19	Power supply wiring and control wiring intake (rear)	$\varnothing$ 29
20	Power supply wiring and control wiring intake (top)	$\varnothing$ 29

**3D106574A**

**NOTES**

1. Location of nameplate. Bottom of the fan housing inside the suction grille
2. When installing a wireless controller, there will be a receiver on this location. For details, see the drawing of the wireless controller.
3. Do not place any objects under the indoor unit. In case of high humidity (>80%), clogged drain outlets, or dirty air filters, condensate may drop out.

**FXHA50-63A**




Item	Name	Description
1	Air discharge grille	
2	Air suction grille	
3	Air filter	
4	Gas pipe	$\varnothing$ 12.7 flare
5	Liquid pipe	$\varnothing$ 6.4 flare
6	Drain pipe connection	VP20
7	Terminal block with earth terminal Located inside of the unit	M4
8	Metal hanger	
9	Position of knockout hole	Rear side
10	Position of knockout hole	Top
11	Piping intake (right)	Knockout hole
12	Drain piping intake (left)	Knockout hole
13	Drain piping intake (right)	Knockout hole
14	Drain piping intake (left-rear)	Knockout hole
15	Standard location of holes in the wall Piping intake (rear)	$\varnothing$ 100
16	Drain piping intake (top)	$\varnothing$ 60
17	Gas piping intake (top)	$\varnothing$ 36
18	Liquid piping intake (top)	$\varnothing$ 26
19	Power supply wiring and control wiring intake (rear)	$\varnothing$ 29
20	Power supply wiring and control wiring intake (top)	$\varnothing$ 29

**3D106552**

**NOTES**

1. Location of nameplate. Bottom of the fan housing inside the suction grille
2. When installing a wireless controller, there will be a receiver on this location. For details, see the drawing of the wireless controller.
3. Do not place any objects under the indoor unit. In case of high humidity (>80%), clogged drain outlets, or dirty air filters, condensate may drop out.

**FXHA100A**




Item	Name	Description
1	Air discharge grille	
2	Air suction grille	
3	Air filter	
4	Gas pipe connection $\varnothing$ 15.9 flare	
5	Liquid pipe connection $\varnothing$ 9.5 flare	
6	Drain pipe connection	VP20
7	Terminal block with earth terminal Located inside of the unit	M4
8	Metal hanger	
9	Position of knockout hole	Rear side
10	Position of knockout hole	Top
11	Piping intake (right)	Knockout hole
12	Drain piping intake (left)	Knockout hole
13	Drain piping intake (right)	Knockout hole
14	Drain piping intake (left-rear)	Knockout hole
15	Standard location of holes in the wall Piping intake (rear)	$\varnothing$ 100
16	Drain piping intake (top)	$\varnothing$ 60
17	Gas piping intake (top)	$\varnothing$ 36
18	Liquid piping intake (top)	$\varnothing$ 26
19	Power supply wiring and control wiring intake (rear)	$\varnothing$ 29
20	Power supply wiring and control wiring intake (top)	$\varnothing$ 29

**3D106530A**

**NOTES**

1. Location of nameplate. Bottom of the fan housing inside the suction grille
2. When installing a wireless controller, there will be a receiver on this location. For details, see the drawing of the wireless controller.
3. Do not place any objects under the indoor unit. In case of high humidity (>80%), clogged drain outlets, or dirty air filters, condensate may drop out.

**FXUA-A**



Model	AA	AB
FXUA50	$\varnothing$ 6.4	$\varnothing$ 12.7
FXUA71	$\varnothing$ 6.4	$\varnothing$ 12.7
FXUA100	$\varnothing$ 9.5	$\varnothing$ 15.9

1	Liquid pipe connection -AA- flare
2	Gas pipe connection -AB- flare
3	VP20 Drain socket
4	Air discharge outlet
5	Air suction grille
6	Corner decoration cover
7	Piping connections / Wiring connection Right side
8	Piping connections / Wiring connection Rear side
9	Pipe cover (top)
10	Drain pipe connection (outside diameter-26)
11	L-type piping kit (upward direction)

**NOTES**

1. The unit nameplate is located on the control box cover.
2. When installing a wireless controller, there will be a receiver on this location. For details, see the drawing of the wireless controller.
3. When closing the discharge grille in case of 2-way blow or 3-way blow, there are limitations to the piping connection direction. See the installation manual. For details, see the drawing of the wireless controller.
4. Do not place any objects under the indoor unit. In case of high humidity (>80%), clogged drain outlets, or dirty air filters, condensate may drop out.

**3D138403**



# Notes

A series of 25 horizontal dotted lines for writing notes.

# Notes

A series of 25 horizontal dotted lines for writing notes.



# Meet our superhero: VRV 5 Heat Recovery




## Purpose-built to support the decarbonisation of commercial buildings

**Support your customers in future-proofing their buildings with  
a breakthrough solution for sustainable climate control.**

Now, more than ever, we all have a part to play in reducing our environmental impact. That's why Daikin is introducing the VRV 5 Heat Recovery unit with innovative new superpowers that make it a future-proof climate solution. Smarter and more responsive than ever – it offers you and your customers complete peace of mind.

Help your customers reduce their CO<sub>2</sub> footprint now while enjoying maximum comfort and ease of use. Visit [www.daikin.eu/VRV5HR](http://www.daikin.eu/VRV5HR) to learn more about the VRV 5 Heat Recovery unit.



**Daikin Europe N.V.** Naamloze Vennootschap Zandvoordestraat 300 · 8400 Oostende · Belgium · [www.daikin.eu](http://www.daikin.eu) · BE 0412 120 336 · RPR Oostende (Publisher)

FSC

ECPEN22-212A

09/2022



The present publication is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this publication to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this publication. All content is copyrighted by Daikin Europe N.V.

Printed on non-chlorinated paper. Prepared by La Movida.